

Miniature Metric Ball Bushing[™] Bearings Smooth Operation, Light Weight and Long Lasting

Thomson Miniature Metric Ball Bushing[™] offer smooth and rapid operation in a light and small package that last up to 27 times longer than conventional linear bearings!

Light weight design

Low inertia enables precision movements and short acceleration times.

Double lip integral wipers

Keeps dirt out, lubrication in and increases life expectancy.

Friction coefficient as low as 0.0001 Eliminates stick-slip and ensure smooth operation.

Four different sizes Select the optimum size for your application parameters. **Super finished bearing plates** Provides smooth operation and long life.

Travel speeds up to 3 m/s Enables short cycle times and rapid adjustments.

Optional corrosion resistant version For use in harsh environments.

Local support around the globe Thomson is a reliable partner with customer support centers all over the world ready to service you!

Contact Thomson today to learn how we can help you make your ball bushing bearing project successfull!





Linear Motion. Optimized.

www.thomsonlinear.com

Engineering Data

Thomson Miniature Ball Bushing[™] bearings are precision components. To preserve bearing warranty you must use Thomson 60 Case LinearRace® shafting. Please contact customer support for additional technical support.





Specifications and Dimensions

Part number (1)			Dimensions [mm]					Number of	Mass	Dynamic	Load	Diametrical clearance (5)	
No integral wiper	One integral wiper	Two integral wipers	d ⁽²⁾	D	C (h14)	C1 (h13)	C2 (min.)	ball tracks	[kg]	load rating ⁽³⁾ [N]	limit ⁽⁴⁾ [N]	House bore (H7) [µm]	House bore (H6) [µm]
MM03	N/A	N/A	3	7	10	-	-	4	0.001	45	50	+25 + 6	+20 +5
MM05	MM05W	MM05WW	5	12	22	14.2	1.10	4	0.010	170	190	+29 +3	+23 +2
MM08	MM08W	MM08WW	8	16	25	16.2	1.10	4	0.020	310	340	+29 +3	+23 +2
MM12	MM12W	MM12WW	12	22	32	22.6	1.30	5	0.040	650	715	+33 +4	+26 +3

(1) For corrosion resistant bearings, add the suffix "-CR" to the part number. Also reduce the above load ratings by 30%.

(2) Nominal LinearRace® diameter.

(3) For a rated travel life of 100 km.

(4) The load limit is the maximum load that may be applied to a bearing/shaft. It is important to analyze the application so that peak or/and shock loads do not exceed the load limit. (5) For ball bushing bearings mounted in a housing and using LinearRace® shafts.

You are welcome to contact your local Thomson office for technical assistance and ordering! Please visit www.thomsonlinear.com for more information about us, our products and services.

USA, CANA	ADA and MEXICO	EUROPE		ASIA			
Thomson		United Kingdom	Phone: +44 (0) 1271 334 500	Asia Pacific	E-mail: sales.hk@thomsonlinear.com		
203A West			E-mail: sales.uk@thomsonlinear.com	China	Phone: +86 400 6661 802 E-mail: sales.china@thomsonlinear.com		
	A 24141, USA	Germany	Phone: +49 (0) 7022 504 0				
Phone:	1-540-633-3549		E-mail: sales.germany@thomsonlinear.com	India	Phone: +91 22 422 70 300		
Fax: E-mail: Literature:	1-540-633-0294 thomson@thomsonlinear.com	France	Phone: +33 (0) 243 50 03 30		E-mail: sales.india@thomsonlinear.com		
	literature.thomsonlinear.com		E-mail: sales.france@thomsonlinear.com	Japan	Phone: +81-6-6386-8001		
		Italy	Phone: +39 0362 594260	oupun	E-mail: csinfo_dicgj@danaher.co.jp		
			E-mail: info@thomsonlinear.it	Korea	Phone: +82 2 547 7807		
		Spain	Phone: +34 (0) 9329 80278	Kuica	E-mail: sales.korea@thomsonlinear.co		
			E-mail: sales.esm@thomsonlinear.com				
		Sweden	Phone: +46 (0) 44 24 67 00				
			E-mail: sales.scandinavia@thomsonlinear.com				

www.thomsonlinear.com

Metric_Miniature_Bearings_BREN-0001-02A | 2013 NOV 12 Specifications are subject to change without notice. It is the responsibility of the product user to determine the suitability of this product for a specific application. All trademarks property of their respective owners. © 2013 Thomson Industries, Inc.

