

Max Jac<sup>®</sup> Electric Linear Actuators Heavy Duty IP69K Actuator for the Toughest Conditions






# Introduction

The Thomson Max Jac<sup>®</sup> linear actuator is the result of decades of extensive success in making linear actuators for the mobile-off-highway market. The Max Jac is built to work virtually maintenance-free in environments where it encounters fertilizers, mud, sand, high pressure water jets, slush, salt water, snow, heat or heavy vibrations.

The Max Jac is not only tough but also a high performer that delivers high speed, efficiency, and accuracy in a compact envelope. Like all Thomson linear actuators, the Max Jac can easily be customized to match your application's requirements.

# Tough, Tougher, Max Jac®

State of the art technology and the best materials available make the Max Jac strong and reliable within a lightweight package. The Max Jac has undergone rigorous testing throughout the entire development process to ensure that it will deliver trouble free operation, long life, and outstanding performance in demanding environments.



## **Max Jac Main Features**

- Long life
- Reliability
- High speed
- High efficiency
- Small envelope
- Minimal backlash

- Vibration resistant
- Duty cycle up to 100%
- Short total length versus stroke
- High degree corrosion protection
- High accuracy position feedback options



# Features and Benefits

The Max Jac<sup>®</sup> can be used in many types of applications, but it excels when used under the harshest conditions. Every aspect of the actuator has been designed to ensure longevity, reliability, and performance.



Let the Max Jac Work in Dust, Dirt, and Mud... The Max Jac electric linear actuator is designed to endure the harshest environments. It is rated for IP66/IP69K and has been tested for 500 hours of salt spray. It withstands dirt, dust and water, and also aggressive substances such as fertilizers, acid, oil, grease, and cleaning agents.

## ... in Arctic to Desert Temperatures ...

The operating temperature range of the Max Jac stretches from -40 to +85 °C which is the greatest range of any actuator on the market. It can operate in almost any place on the Earth whether it be in the arctic region or in a desert.

## ... and Just Wash it Off!

Unlike most actuators the Max Jac can be washed directly with high pressure water jets and even be submerged for short periods when not operating. This eliminates the need for bellows or other protective devices. The Max Jac simplifies cleaning and installation, reduces the size of the installation, and lowers the total cost.

# Features, Benefits and Applications

## **Best In Class**

The Max Jac<sup>®</sup> is the best overall choice among actuators when designing for demanding applications. It offers the following advantages:

- Shortest overall length versus stroke
- Fastest among its peers
- Resistant against vibration and impacts
- Largest operating temperature range
- Possibility to work at 100% duty cycle
- Long and completely maintenance free life.

## **Non-Contact Position Feedback Options**

The Max Jac can be equipped with two kinds of position feedback options that fit in to the standard housing without adding to the outer dimensions:

- Analog position output signal
- Digital encoder output.

Both use non-contact position sensors which ensure that the life of the position feedback device is at least as long as the life of the actuator itself. It also means that the signal does not vary over time due to wear and the system therefore never requires any re-calibration.

## Worm or Ball Screw Models

Max Jac is available with either worm or ball screws, each with unique advantages. The worm screw version is self-locking and will not back drive on power-off. The ball screw version will go faster, take higher loads and operate at higher duty cycles.

## **Suitable for Pneumatic Conversion**

Compared to pneumatic cylinders, electric linear actuators:

- Are easier to install
- Offer more control options
- Reduce energy costs.

The Max Jac has many properties that make it suitable for pneumatic conversion. It is:

- Fast
- Small

- Long life
- High duty cycle
- Able to withstand harsh environments.

Typical applications where the Max Jac can replace pneumatic cylinders are found in the food, packaging and handling industries and in all types of vehicles, construction and farming equipment.

# **Applications**

The Max Jac<sup>®</sup> is the ideal choice whenever the environment is tough and wherever long life and trouble free operation is essential. The Max Jac is specifically designed to be used in applications that need:

- High duty cycles
- Accuracy
- Ability to withstand water
- Ability to withstand aggressive chemicals.

The Max Jac can be used to control sand/salt/ fertilizer spreaders, hatches, doors and throttles and is ideal in vehicles used for:

- Farming equipment
- Road maintenance
- Construction work
- Military.

The Max Jac linear actuator is also an excellent choice for yacht, ship and oil platform applications due it's ability to withstand water, salt and chemicals as well as its great operating temperature range. Other suitable application areas include:

- Food industry
- Trains and trams
- Mining equipment.



# Specifications



## Standard Features and Benefits

- Designed for industrial applications
- Rugged aluminum housing with IP69K
- High efficiency
- Long life
- Hard coat anodizing for high corrosion resistance
- Virtually maintenance free
- Worm or ball screw models
- Non-contact analog position feedback signal

General Specifications					
Parameter	Max Jac				
Screw type	worm or ball				
Internally restrained	no				
Manual override	no				
Dynamic braking	no				
Self-locking worm screw models ball screw models	yes no				
End of stroke protection	no				
Mid stroke protection	no				
Motor protection	no				
Motor connection	flying leads or cable with connector				
Motor connector	AMP Superseal Series 1.5				
Certificates	CE				
Options	Encoder position feedback				

# Performance Specifications


1		
Parameter		Max Jac
Maximum load, dynamic / static MX • • W (worm screw) MX • • B (ball screw)	[N]	500 / 2000 800 / 100 - 350 <sup>(1)</sup>
Speed, at no load / at maximum load MX • • W (worm screw) MX • • B (ball screw)	[mm/s]	33 / 19 60 / 30
Available input voltages	[VDC]	12, 24
Standard stroke lengths	[mm]	50,100,150 200, 250 <sup>(2)</sup> , 300 <sup>(2)</sup>
Operating temperature limits	[°C]	-40 to +85
Full load duty cycle @ 25 °C	[%]	25
End play, maximum	[mm]	0.3
Restraining torque	[Nm]	2
Lead cross section	[mm <sup>2</sup> ]	1
Standard cable lengths	[mm]	300, 1600
Protection class		IP66/IP69K
Salt spray resistance	[h]	500
Life	[cycles]	500000 <sup>(3)</sup>
Analog position feedback signal	[VDC]	0.5 - 4.5
Encoder position feedback option Supply voltage Pulses per mm, worm / ball screw Channels	[VDC]	5 9.86 / 5.84 A, B

<sup>(1)</sup> The static force (i.e. the back-driving force) for a ball screw unit varies and is dependent on the number of cycles it has been running and at which loads.


 $\ensuremath{^{(2)}}$  Strokes possible for ball screw models only.


<sup>(3)</sup> For ball screw actuator with 100 mm stroke, average load of 500 N and changing load direction.

## Duty Cycle vs. Load



www.thomsonlinear.com








Stroke (S)	[mm (inch)]	[mm (inch)] 50 (1.97)		150 (5.91)	200 (7.87)	250 (9.84) *	300 (11.81) *	
Retracted length (A)	[mm (inch)]	206 (8.11)	256 (10.08)	306 (12.05)	356 (14.02)	406 (15.98)	456 (17.95)	
Weight	[kg]	1.5	1.7	1.9	2.1	2.2	2.4	

\* Strokes possible for ball screw models only.



Ordering	Key

**Performance Diagrams** 

Position	1 2		2		3		4	5	
Example	MX12-	В	8 M15			Р	1		
1. Actuator type and supply voltage   MX12- = Max Jac 12 VDC   MX24- = Max Jac 24 VDC   2. Max. dynamic load, screw type and max. speed   B8 = 800 N, ball screw, 55 mm/s   W1 = 500 N, worm screw, 35 mm/s		3. Stroke (S) M05 = 50 mm M10 = 100 mm M15 = 150 mm M20 = 200 mm M25 = 250 mm* M30 = 300 mm*		4. Position feedba P = analog signal E = encoder signa	(standard)	1 = 300 mm l 2 = 1600 mm	connectors ong flying leads ong cable and connector ** long cable and connector ** seal series 1.5 connector		

\* Strokes possible for ball screw models only.

www.thomsonlinear.com

### EUROPE

United Kingdom Thomson Office 9, The Barns Caddsdown Business Park Bideford Devon, EX39 3BT Phone: +44 (0) 1271 334 500 E-mail: sales.uk@thomsonlinear.com

### Germany

Thomson Nürtinger Straße 70 72649 Wolfschlugen Phone: +49 (0) 7022 504 0 Fax: +49 (0) 7022 504 405 E-mail: sales.germany@thomsonlinear.com

#### France

Thomson Phone: +33 (0) 243 50 03 30 Fax: +33 (0) 243 50 03 39 E-mail: sales.france@thomsonlinear.com

#### Italy

Thomson Largo Brughetti 20030 Bovisio Masciago Phone: +39 0362 594260 Fax: +39 0362 594263 E-mail: sales.italy@thomsonlinear.com

### Spain

Thomson E-mail: sales.esm@thomsonlinear.com

#### Sweden

Thomson Estridsväg 10 29109 Kristianstad Phone: +46 (0) 44 24 67 00 Fax: +46 (0) 44 24 40 85 E-mail: sales.scandinavia@thomsonlinear.com

#### **SOUTH AMERICA**

**Brasil** Thomson Av. Tamboré, 1077 Barueri, SP – 06460-000 Phone: +55 (11) 3616-0191 Fax: +55 (11) 3611-1982 E-mail: sales.brasil@thomsonlinear.com

#### **USA, CANADA and MEXICO**

Thomson 203A West Rock Road Radford, VA 24141, USA Phone: 1-540-633-3549 Fax: 1-540-633-0294 E-mail: thomson@thomsonlinear.com Literature: literature.thomsonlinear.com

### ASIA

Asia Pacific Thomson E-mail: sales.apac@thomsonlinear.com

## China

Thomson Rm 2205, Scitech Tower 22 Jianguomen Wai Street Beijing 100004 Phone: +86 400 6661 802 Fax: +86 10 6515 0263 E-mail: sales.china@thomsonlinear.com

## India

Thomson c/o Fluke Technologies Pvt. Ltd. #424, Deodhar Center, Marol Maroshi Road, Andheri – E, Mumbai – 400059 India Phone: +91 22 29207641 E-mail: sales.india@thomsonlinear.com

## Japan

Thomson Minami-Kaneden 2-12-23, Suita Osaka 564-0044 Japan Phone: +81-6-6386-8001 Fax: +81-6-6386-5022 E-mail: csjapan@scgap.com

## Korea

Thomson F7 Ilsong Bldg, 157-37 Samsung-dong, Kangnam-gu, Seoul, Korea (135-090) Phone: +82 2 6917 5049 Fax: +82 2 528 1456 E-mail: sales.korea@thomsonlinear.com

www.thomsonlinear.com

Max\_Jac\_BRUK-0003-04B | 20160919SK Errors and technical alterations reserved. It is the responsibility of the product user to determine the suitability of this product for a specific application. All trademarks property of their respective owners. © 2016 Thomson Industries, Inc.

