

Precision Linear Actuators





Presentation

Thomson

Thomson is one of the leading suppliers of mechanical motion control products in the world. Linear actuators, linear motion systems, lead screws, clutches, brakes and linear guides are just some of the products manufactured by Thomson. Thomson has plants, support centers and sales offices all around the globe. In addition we have a large network of distributors and system houses that all are ready to support you throughout the entire life cycle of the product.

Precision linear actuators

The precision linear actuator range is a result of over 40 years of actuator development and represents the state of the art in linear actuator design. Designed for the most demanding applications they are ideal when the maximum available performance and longest life cycle are required. Thomson precision linear actuators guarantees trouble-free operation even in the toughest applications.

Perfect your own actuator or chose a packaged model

The precision linear actuators are divided in to two categories. The T-series which consist of the basic actuator that is equipped by the customer with motors and gears of his own choice, either bought from Thomson or sourced from his own suppliers allowing maximun freedom of choice. The ECT-series is a range of packaged and predefined actuators that comes with motors and gears mounted and tested. The ECT-series gives the benefit of knowing that all performance data has been verified in tests and that all components works together perfectly. An added bonus is of course the faster design and ordering process and the benefit of dealing with one supplier only.

On-line selection software

On www.thomsonlinear.com/selectors you can select a precision linear actuator by using the PLA advisor. This easy to use software lets you play with all the parameters and will give you all the relevant data and the correct ordering information for your choice.



Features and Benefits

Precision linear actuators are ideal for positioning loads that are either externally-guided and supported, or pivoting. They are also ideal where there is a high concentration of airborne contaminants, as rodless actuators are inherently less well protected. Another suitable area is the replacement of hydraulic or pneumatic cylinders where they bring many benefits compared to the traditional technologies.

Handling, machining and manufacturing

Precision linear actuators can successfully be used in handling, machining and manufacturing applications. The broad range of options and accessories makes it easy to find the perfect actuator for most applications.

Strong, fast and accurate

The hallmark for the entire range of precision linear actuators is the ability to work hard, fast and accurately, day in and day out, under the toughest conditions.

Hydraulics and pneumatics replacement

Precision linear actuators are direct descendants of hydraulic and pneumatic cylinders. Possessing many of the same unique design characteristics that made hydraulic and pneumatic cylinders popular, actuators benefit from cleaner, simpler and more energy-efficient power transmission. They are also much easier to integrate with modern programmable controls, have greater accuracy and are less noisy.

Harsh environments

Chemical plants, paper mills, welding operations and outdoor applications are all suitable for precision linear actuators. IP65 protection, a robust design and the use of high-quality components makes them suitable for almost every location.

Minimum maintenance

All precision linear actuators are designed to require a minimum of maintenance. There are no parts that need to be replaced due to wear. And only in applications where the actuators need to work very hard and frequently will any regular lubrication be needed.

Customized units

Customization is one of our strengths. Do you need a special stroke, a unique mounting bracket or some other adaptation of the standard product? No problem. Just contact us and we will be glad to help you to find the perfect solution to your application.













Performance Overview

		T60	T90	T130	
Load					
Maximum load, Fx	[N]	10 000	20 000	60 000	
Maximum load, Fy	[N]	100	500	800	
Maximum load, Fz	[N]	100	500	800	
Maximum load torque, Mx	[Nm]	-	-	-	
Maximum load torque, My	[Nm]	50	150	300	
Maximum load torque, Mz	[Nm]	50	150	300	
Stroke					
Maximum standard stroke	[mm]	1500	1500	2000	
Speed					
Maximum speed	[m/s]	2,5	2,0	2,0	
Accuracy					
Repeatability	[±	0,05	0,05	0,05	
Backlash	[mm]	0,11	0,11 (0,18) ¹	0,21	
General data					
Profile size (width × height)	[mm]	75 × 60	90 × 92	130 × 130	
Operating temperature limits	[°C]	-20 — +70	-20 — +70	-20 — +70	
Maximum duty cycle	[%]	100	100	100	
Lead screw diameter	[mm]	25	25, 32	40, 50	
Lead screw type		ball screw	ball screw	ball screw	
Protection class - standard / optional		IP65	IP65	IP65	
Features					
AC servo motor / Three phase AC motor		-	-	-	
Single point lubrication		•	•	•	
Mounting options					
Magnetic position sensors		•	•	•	
Mounting feet kit		on request	•	•	
Trunnion mounting kit		•	•	•	
Clevis mounting kit		•	•	•	
Tube end - inside / outside thread / spherical joint		-/•/•	•/•/•	•/•/•	

¹ Depending on the screw diameter used in the actuator.


ECT90	ECT130
20 000	38 000
500	800
500	800
-	-
150	300
150	300
1500	2000
	2555
1,6	2,0
0,05	0,05
0,11 (0,18) ¹	0,21
90 × 92	130 × 130
-20 - +70	-20 - +70
100	100
25, 32	40
ball screw	ball screw
IP65	IP65
•/•	•/•
•	•
•	•
•	•
•	•
•/•/•	•/•/•
1 1	1 1



Technical Overview

The design of an precision linear actuator is quite basic. An electric motor – through either a belt gear, a worm gear, a planetary gear or via a coupling directly – rotates a ball screw which translates the torque into axial force through the extension tube. While the concept is straight

forward, as illustrated by the cutaway on this page, significant expertise and development have been invested in the specification and design of each component. Each actuator is also built to meet the highest quality standards and are thoroughly tested before shipment.





- 1. Choose between a high performance AC servo motor or the robust, cheaper and simpler three phase AC motor.
- 2. High quality extension tube in extruded aluminium with grooves for sensors and T-slot bolts.
- 3. One point lubrication for easy and fast service.
- 4. Robust hard chromed steel extension tube.
- 5. Choose between extension tube with inside or outside thread, clevis or spherical joint ends.
- 6. Choose between direct drive, belt gear, worm gear or planetary gear for optimum performance.
- 7. High precision safety ball nut that will hold the load even if the balls break.
- 8. High quality ball screw drive.
- 9. Internally guided extension tube with anti-rotation mechanism which also acts as a screw support.
- 10. IP65 sealing of the actuator allows it to operate in harsh environments.


Applications


The precision linear actuator range is used for many tasks in industry. Combining the actuators with controls and drives from Kollmorgen makes it easy to design linear motion equipment in a fast and simple way. Some of the most common applications are described below.


Our application engineers have a broad knowledge base built on decades of linear motion experience and they can help you find the ultimate solution for your application. They can also assist you with sizing and selection as well as with the design and commissioning of your equipment.













Drilling, Welding, Gluing or Thermo-forming

- Machine tools
- Plastic industry

Backstop Adjust

· Wood work industry

- Metal industry
- Wood work industry
- Electronic industry
- Packaging industry

EUROPE

United Kingdom

Thomson Fishleigh Road Barnstaple

EX31 3UD, United Kingdom Phone: +44 (0)1271 334 500 +44 (0)1271 334 501 Fax:

E-mail: sales.uk@thomsonlinear.com

Germany

Thomson

Nürtinger Straße 70

72649 Wolfschlugen, Germany Phone: +49 (0) 7022 504 100 +49 (0) 7022 504 405 Fax:

E-Mail: sales.wolfschlugen@thomsonlinear.com

Sweden

Thomson Box 9053

SE-291 09 Kristianstad, Sweden Phone: +46 (0) 44-24 67 00 Fax: +46 (0) 44-24 40 85

E-mail: sales.scandinavia@thomsonlinear.com

Italy

Thomson Largo Brughetti

I-20030 Bovisio Masciago, Italy Phone: +39 0362 594260 +39 0362 594263 Fax: E-mail: info@thomsonlinear.it

France

Thomson C.P 80018

12, Rue Antoine Becquerel – Z.I. Sud F-72026 Le Mans Cedex 2, France Phone: +33 (0) 243 50 03 30

+33 (0) 243 50 03 39 Fax:

E-mail: sales.france@thomsonlinear.com

Spain

Thomson

Rbla Badal, 29-31 7th, 1st 08014 Barcelona, Spain Phone: +34 (0) 9329 80278 +34 (0) 9329 80278 Fax:

E-mail: josep.estaran@thomsonlinear.com

USA, CANADA and MEXICO

Thomson

203A West Rock Road Radford, VA 24141, USA Phone: 1-540-633-3549 1-540-633-0294 Fax:

F-mail: thomson@thomsonlinear.com Literature: literature.thomsonlinear.com

ASIA

China

Thomson

Room 2206, Scitech Tower No 22

Jianguomenwai Avenue, Beijing100004, China

Hotline: +86 400 666 1802 +86 10 65120195 Tel: Fax: +86 10 65150506 Email: tm.sales@danaher.com

Japan

Thomson

2F, Sigma Hatchobori Bldg 2-7-1 Hatchobori Chuo-ku Tokyo 104-0032, Japan Phone: +81-3-6222-1051 +81-3-6222-1055 Fax:

E-mail: info@danahermotion.co.jp

Asia Pacific

Thomson

Unit A, 16 Floor, 169 Electric Road Manulife Tower, North Point, Hong Kong

+852 2503 6581 Phone: Fax: +852 2571 8585

E-mail: victor.lim@thomsonlinear.com

Korea

Thomson

Room No. 715, Western Tower II 867 Janghang-dong, Llsandong-gu Koyang-city Kyunggi-do, 410-380, Korea

Phone: +82 31 931 5170 Fax: +82 31 931 5176

koreainfo@thomsonlinear.com E-mail:

India

Thomson Unit No 2, SDF 1

Seepz Andheri, Mumbai 400 096, India

Phone: +91 22 28294058 Fax: +91 22 28394036

E-mail: girish.mahajani@danahermotion.com EU200608-08 16nov2009 GB Information & specifications subject to change at any time. Printed in Germany. © Thomson GmbH 2010