




MOUNTING OF A MOTOR AND FLANGE TO A LINEAR MOTION SYSTEM .

# Mounting a drive motor to the flange of a linear motion system

The electrical installation and the checking of the direction of rotation may only be carried out by a licensed electrician. Always check the direction of motor rotation in association with the safety limit switches (if necessary, change the direction of rotation by connecting the motor differently) before mounting the motor. Then proceed as described below:

- 1. Attach the coupling half (4) to the drive shaft of the linear motion system.
- 2. Attach the motor adapter flange (5) to the flange of the linear motion system (6) with four screws.
- 3. Push the toothed wheel (3) onto the coupling half on the linear motion system.
- 4. Mount the second coupling half (2) on the drive shaft of the motor (1).
- 5. Attach the motor with the coupling half to the motor adapter flange (5) with four screws. Ensure that no axial pressure is exerted on the motor shaft. If necessary, correct the distance between the two coupling halves.



- 1. Motor
- 2. Coupling half
- 3. Toothed wheel
- 4. Coupling half
- 5. Adapter flange
- 6. Flange

Make sure all bolts and screws are tightened according to the tables on the next page.

# **Tightening torque tables**

TABLE 1:ROTEX GS TYPE 1.0/1.1


RotexGS size	Setscrew	Tightening torque
5	M2	2,5 Nm
7	М3	3,5 Nm
9, 12, 14	M4	5,0 Nm
19, 24	M5	10 Nm
28, 38	М8	15 Nm
42, 48	M8	20 Nm
55, 65	M10	20 Nm
75	M10	25 Nm

TABLE 2: ROTEX GS TYPE 2.0/2.1/2.5/2.6/4.0/5.0/6.0/6.5


RotexGS size	Clamp.screw	Tightening torque
5	M1,2	- Nm
7	M2	0,37 Nm
9	M2,5	0,76 Nm
12, 14	М3	1,34 Nm
19, 24	M6	10,5 Nm
28, 38	M8	25 Nm
42	M10	69 Nm
48, 55, 65	M12	120 Nm
75	M16	295 Nm

TABLE 3: FASTENING SCREW


Screw Dim.	Quality	Tightening torque
М3	8.8	1,35 Nm
M4	8.8	3,3 Nm
M5	8.8	6,5 Nm
М6	8.8	11,1 Nm
М8	8.8	26,6 Nm
M10	8.8	52,5 Nm
M12	8.8	91,2 Nm
M14	8.8	145 Nm



ROTEX GS TYPE 1.0/1.1



ROTEX GS TYPE 2.0/2.1/2.5/2.6



ROTEX GS TYPE 4.0/5.0/6.0/6.5



Technical changes to improve the performance of the equipment may be made without notice! All rights reserved. No part of this work may be reproduced in any form (by printing, photocopying, microfilm or any other method) or processed, copied or distributed by electronic means without the written permission of Thomson.

### EUROPE

### **United Kingdom**

Thomson Office 9, The Barns Caddsdown Business Park Bideford

Devon, EX39 3BT Phone: +44 (0) 1271 334 500 E-mail: sales.uk@thomsonlinear.com

#### Germany

Thomson Nürtinger Straße 70 72649 Wolfschlugen Phone: +49 (0) 7022 504 0 Fax: +49 (0) 7022 504 405

E-mail: sales.germany@thomsonlinear.com

#### France

Thomson

Phone: +33 (0) 243 50 03 30 Fax: +33 (0) 243 50 03 39

E-mail: sales.france@thomsonlinear.com

# Italy

Thomson Largo Brughetti 20030 Bovisio Masciago Phone: +39 0362 594260 Fax: +39 0362 594263 E-mail: info@thomsonlinear.it

### Spain

Thomson

E-mail: sales.esm@thpmsonlinear.com

### Sweden

Thomson Estridsväg 10 29109 Kristianstad Phone: +46 (0) 44 24 67 00 Fax: +46 (0) 44 24 40 85

E-mail: sales.scandinavia@thomsonlinear.com

#### SOUTH AMERICA

### Brazil

Thomson Av. Tamboré, 1077 Barueri, SP – 06460-000 Phone: +55 (11) 3616-0191 Fax: +55 (11) 3611-1982

E-mail: sales.brasil@thomsonlinear.com

## USA, CANADA and MEXICO

Thomson 203A West Rock Road Radford, VA 24141, USA Phone: 1-540-633-3549 Fax: 1-540-633-0294

E-mail: thomson@thomsonlinear.com Literature: literature.thomsonlinear.com

#### ASIA

## Asia Pacific

Thomson

E-mail: sales.apac@thomsonlinear.com

### China

Thomson

Rm 2205, Scitech Tower 22 Jianguomen Wai Street Beijing 100004

Phone: +86 400 6661 802 Fax: +86 10 6515 0263

E-mail: sales.china@thomsonlinear.com

#### India

Thomson c/o Fluke Technologies Pvt. Ltd. #424, Deodhar Center, Marol Maroshi Road, Andheri – E, Mumbai – 400059 India

Phone: +91 22 29207641

E-mail: sales.india@thomsonlinear.com

#### Japan

Thomson Minami-Kaneden 2-12-23, Suita Osaka 564-0044 Japan Phone: +81-6-6386-8001 Fax: +81-6-6386-5022 E-mail: csjapan@scgap.com

#### Korea

Thomson F7 Ilsong Bldg, 157-37 Samsung-dong, Kangnam-gu, Seoul, Korea (135-090) Phone: +82 2 6917 5049 Fax: +82 2 528 1456

E-mail: sales.korea@thomsonliear.com