

SA-20 Stainless Steel Linear Actuators

Hygienic Electromechanical Actuators for the Food and Beverage Industry





Thomson SA-20 Stainless Steel Food Grade Actuators

SA-20 stainless steel linear actuators conform to several hygienic design guidelines, including 3-A Dairy for the food and beverage industry, and are IP69K rated, enabling sanitary washdown during operation.

SA-20 actuators are suited for a wide variety of applications where reliability, durability, hygiene and corrosion resistance are critical.

- FDA-compliant exterior components
- Hardened, alloy steel ball screws
- Angular contact bearings minimize wear and extend operation life
- Clean in place (CIP) while actuator is operating
- 316 stainless housing for corrosion resistance
- Several mounting options
- Water and dust resistant (IP69K)
- Reduces the need for protective guards

Applications

Designed as an alternative to pneumatic cylinders in food and beverage applications, Thomson SA-20 actuators reduce total cost of washdown, including maintenance and air, and eliminate the need for replacement due to leakage. These advantages make them perfect for:

- Conveyors
- Cutting, slicing, filling and dumping
- Operating doors, hatches and lids
- Packaging
- Sorting
- Lifting, positioning, pushing and tilting







2 www.thomsonlinear.com


Technical Specifications

General Specifications		
Parameter	SA-20	
Screw type	ball	
Nut type	ball nut	
Motor configuration	inline	
Anti-rotation	yes	
End-of-stroke protection	no	
External component material	316 S/S	
Front adapters	threaded hole or threaded pin	
Rear adapter	trunnion	
Compliances	NSF/ANSI/3-A SSI 14159-1 — 2014 FDA 21 CFR, Parts 177 & 178	

Life Expectancy - Example Case Calculation			
SA-20			
os] 230 / 450			
in] 1208 689 488			
in) 201 488 248			
40			
ur] 83937			
ar] 16.8			

Mechanical Specifications			
Parameter		SA-20	
Max. dynamic load (Fx) screw lead 0.2 in screw lead 0.5 in screw lead 5 mm screw lead 20 mm	[N (lbf)]	5783 (1300) 5783 (1300) 5783 (1300) 5783 (1300)	
Max. linear speed screw lead 0.2 in screw lead 0.5 in screw lead 5 mm screw lead 20 mm	[mm/s (in/s)]	254 (10) 635 (25) 250 (9.84) 1000 (39.37)	
Max. input speed	[rpm]	3000	
Ordering stroke (S) lengths	[mm]	150 - 750	
Ordering stroke length increments	[mm]	150	
Operating temperature limits	[°C (F)]	4-49 (40-120)	
Full load duty cycle	[%]	100	
Protection class		IP69K	
Food zone rating		contact	

Dimensions



Shown with threaded hole front adapter.

Dimensions of dotted portions are dependent upon which motors and flanges are selected by the customer.

Dimensions [mm (in)]		
и	L2	Х
329.2 (12.96) + ordering stroke	L1 + 0.3 (0.01)	5/8"-18 UNF-2B female thread or M16 x 2.0 $-$ 6H metric female thread

www.thomsonlinear.com 3

USA, CANADA and MEXICO

Thomson

203A West Rock Road Radford, VA 24141, USA Phone: +1 540 633 3549 Fax: 1 540 633 0294

E-mail: thomson@thomsonlinear.com Literature: literature.thomsonlinear.com

EUROPE

United Kingdom

Thomson Office 9, The Barns Caddsdown Business Park Bideford, Devon, EX39 3BT Phone: +44 1271 334 500

E-mail: sales.uk@thomsonlinear.com

Germany

Thomson

Nürtinger Straße 70 72649 Wolfschlugen Phone: +49 7022 504 403 Fax: +49 7022 504 405

E-mail: sales.germany@thomsonlinear.com

France

Thomson

Phone: +33 243 50 03 30 Fax: +33 243 50 03 39

E-mail: sales.france@thomsonlinear.com

Italy

Kollmorgen srl Via per Cinisello 95/97 20834 Nova Milanese (MB) Phone: +39 0362 594260 / 366406 Fax: +39 0362 276790

Spain

Thomson

E-mail: sales.esm@thomsonlinear.com

E-mail: sales.italy@thomsonlinear.com

Sweden

Thomson Estridsväg 10 29109 Kristianstad Phone: +46 44 59 02 400

Fax: +46 44 24 40 85

E-mail: sales.scandinavia@thomsonlinear.com

ASIA

Asia Pacific

Thomson

E-mail: sales.apac@thomsonlinear.com

China

Thomson Rm 805, Scitech Tower 22 Jianguomen Wai Street Beijing 100004

Phone: +86 400 606 1805 Fax: +86 10 6515 0263

E-mail: sales.china@thomsonlinear.com

India

Thomson

c/o Portescap India Pvt Ltd 1 E, first floor, Arena House Road no 12, Marol Industrial Area, Andheri (E), Mumbai 400093 India E-mail: sales.india@thomsonlinear.com

Japan

Thomson Minami-Kaneden 2-12-23, Suita Osaka 564-0044 Japan

Phone: +81 6 6386 8001 Fax: +81 6 6386 5022 E-mail: csjapan@scgap.com

South Korea

Thomson 3033 ASEM Tower (Samsung-dong) 517 Yeongdong-daero

Gangnam-gu, Seoul, South Korea (06164) Phone: + 82 2 6001 3223 & 3244

E-mail: sales.korea@thomsonlinear.com

SOUTH AMERICA

Brasil

Thomson

Av. João Paulo Ablas, 2970

Jardim da Glória - Cotia SP - CEP: 06711-250

Phone: +55 11 4615 6300

 $\hbox{E-mail: sales.brasil@thomsonlinear.com}$

