
## MovoTrak™ Cobot Transfer Unit



# Get moving with the first collaborative 7th axis

The Thomson MovoTrak cobot transfer unit (CTU) is a plug-and-play system with up to 10 meters of horizontal operating range, which can help boost productivity for various robotic functions. With flexible mounting options, it's compatible with the largest sized cobots on the market, including Universal Robots' UR20.



#### Features & Benefits

- User-adjustable collision detection settings allow users to set the sensitivity of the 7<sup>th</sup> axis per the application requirements.
- Collision monitoring/safeguard stops initiated through digital I/O with minimal processing required from the UR controller.
- Freedrive allows hand-driven movements to set linear waypoints during programming.
- Dual-linear-unit design delivers maximum moment load and stiffness, even when the cobot arm is fully extended.

### **Applications**

- Machine tending
- Material handling (bin picking, palletizing and packaging)
- Large-scale welding, soldering, sanding and dispensing

#### Additional Resources

- Watch the MovoTrak CTU in action
- Sign up for live training/virtual design consultation










### 7th Axis Mechanical Assembly



## Assembly includes MovoTrak control box and URCap with 7th axis sensitivity adjustment





## **Ordering Key**

3 - 7					
Position	1	2	3	4	5
Example	CTU07	В	R	02000	UR10
1. CTU type and size CTU07 = MovoTrak CTU size 07 (Movopart M75 linear unit)  2. Drive type B = belt drive left / right  3. Motor configuration L = motor on left side R = motor on right side		4. Stroke length xxxxx = stroke in millimeters  5. Type and size of articulated robot UR03 = Universal Robot UR3e UR05 = Universal Robot UR5e UR10 = Universal Robot UR10e UR16 = Universal Robot UR16e UR20 = Universal Robot UR20			

#### **Notes**

- Repeatability of ±25 μm/m of stroke.
- Light washdown options available. Contact Thomson for details.

#### thomsonlinear.com