

FluoroNyliner 1VA

Linear Guide #5 Corrosive/Contaminated Environments



INCH



FluoroNyliner* L	inear Guide 1V	(Dimensions in inches)						
Part	Nominal	L1	Н	Br	В9	Pillow	Shaft	
Number	Diameter					Block	Support	
							Rail	
							Assembly	
1VA-08-FAO	.50	1.50	1.812	1.50	2.00	FNYBUPBO08A-XS	SRA-8-XS-SS	
1VA-12-FAO	.75	1.88	2.437	1.75	2.75	FNYBUPBO12A-XS	SRA-12-XS-SS	
1VA-16-FAO	1.00	2.63	2.937	2.13	3.25	FNYBUPBO16A-XS	SRA-16-XS-SS	
1VA-20-FAO	1.25	3.38	3.625	2.50	4.00	FNYBUPBO20A-XS	SRA-20-XS-SS	
1VA-24-FAO	1.50	3.75	4.250	3.00	4.75	FNYBUPBO24A-XS	SRA-24-XS-SS	

FluoroNyliner Lir	FluoroNyliner Linear Guide 1VA Single Continuously Supported with 1 Twin Pillow Block (Dimensions in inches)											
Part	Nominal	L2	Н	Br	B9	Maximum	Pillow	Shaft				
Number	Diameter					Stroke	Block	Support				
						Length		Rail				
								Assembly				
1VA-08-HAO	.50	3.5	1.812	1.50	2.00	L-(3.5)	FNYBUTWNO08A-XS	SRA-8-XS-SS				
1VA-12-HAO	.75	4.5	2.437	1.75	2.75	L-(4.5)	FNYBUTWNO10A-XS	SRA-12-XS-SS				
1VA-16-HAO	1.00	6.0	2.937	2.13	3.25	L-(6.0)	FNYBUTWNO16A-XS	SRA-16-XS-SS				
1VA-20-HAO	1.25	7.5	3.625	2.50	4.00	L-(7.5)	FNYBUTWNO20A-XS	SRA-20-XS-SS				
1VA-24-HAO	1.50	9.0	4.250	3.00	4.75	L-(9.0)	FNYBUTWNO24A-XS	SRA-24-XS-SS				

Maximum Operating Parameters per Bearing

1 3	1 3
Characteristic	Limit
Liner Temperature Range	-240° C to 288° C (-400° F to 550° F)
Velocity, dry	42.7 m/min. Continuous
Velocity, dry	122 m/min. Intermittent
Velocity, lubricated	122 m/min. Continuous
Pressure	10.35 MPa
PV	21 MPa/m/min

FluoroNyliner* Linear Guide **1VA Benefits:**

- Requires only one part number to specify the entire linear guide.
- Used as a load support, transport, and guidance solution.
- Used in continuously supported applications when rigidity is required.

FluoroNyliner Linear Guide **1VA Components:**

- 2 self-aligning FluoroNyliner* Bushing bearing open pillow blocks or 1 self-aligning FluoroNyliner Bushing bearing open twin pillow block.
- 1 stainless steel 60 Case* linearRace* shaft support rail assembly.


Specifying this Thomson Linear Guide:

1. Determine the proper Linear Guide for your load and life requirements. 2. Select the part number. 3. Add the letter "L" followed by the overall length in inches, as a suffix to the part number.

Part Numbering System

1VA-12-FAO L24

Linear Guide Linear Guide Designation -- Length Nominal Diameter Type of Bearing Block Type of Support



	Lubrication	‡	Polpol		⊫-Br-≠								
Self-Aligning Pillow Blocks (Dimensions in inches)													
Part	Nom.	L1	H9	H8	H5	B9	B8	B7	J	J1	F		Wt.
Number	Dia.										Bolt	Hole	lb
FNYBUPBO08A-XS	.50	1.50	1.12	.687	.25	2.00	.75	.69	1.69	1.00	#6	.16	.20
FNYBUPBO12A-XS	.75	1.88	1.56	.937	.31	2.75	1.00	.94	2.38	1.25	#8	.19	.51
FNYBUPBO16A-XS	1.00	2.63	2.00	1.187	.38	3.25	1.25	1.19	2.88	1.75	#10	.22	1.03

4.00

4.75

1.63

1.88

1.50

1.75

Housing Material: Aluminum Alloy Black Anodized

1.25

1.50

3.38

3.75

2.56

2.94

1.500

1.750

.43

.50

FNYBUPBO20A-XS

FNYBUPBO24A-XS

Self-Aligning Twin Pillow Blocks									
Part Number	Nom. Dia.	L2	J3	Wt. Ib.					
FNYBUTWNO08A-XS	.500	3.50	2.50	.40					
FNYBUTWNO12A-XS	.750	4.50	3.50	1.02					
FNYBUTWNO16A-XS	1.00	6.00	4.50	2.06					
FNYBUTWNO20A-XS	1.25	7.50	5.50	4.30					
FNYBUTWNO24A-XS	1.50	9.00	6.50	6.88					

Housing Material: Aluminum Alloy Black Anodized

Performance Note: For detailed explanations of FluoroNyliner Linear Guide Dynamic and Static Load Capacities, Frictional Characteristics, Wear Rates, Speeds, and Life Expectancy please contact Thomson Linear Guides Applications Engineering department.

3.50

4.12

2.00

2.50

#10

1/4

.22

.28

2.15

3.29

Product Note: FluoroNyliner linear guides are shipped free of all lubricants. It is the responsibility of the product user to determine lubricant compatibility with the FluoroNyliner bearing material.

Product Options: FluoroNyliner linear guides are available with various inner race materials and platings to accommodate different environments.

Type SRA LinearRace Shaft Support Rail Assembly (Dimensions in Inches)										
Part	Nom.	H1	H7	Br	K	Х	Υ	(Wt.	
Number	Dia.							Bolt	Hole	lb/ft
SRA-8-XS-SS	.50	1.125	.19	1.50	1.00	4	2	#6	.17	1.26
SRA-12-XS-SS	.75	1.500	.25	1.75	1.25	6	3	#10	.22	2.50
SRA-16-XS-SS	1.00	1.750	.25	2.13	1.50	6	3	1/4	.28	4.06
SRA-20-XS-SS	1.25	2.125	.31	2.50	1.88	6	3	⁵ /16	.34	6.30
SRA-24-XS-SS	1.50	2.500	.38	3.00	2.25	8	4	⁵ /16	.34	8.60

LinearRace Support Rail Material: Aluminum Alloy Black Anodized