

MICRON

TRUE Planetary[™] **Gearheads**



Product Overview

NemaTRUETM

DuraTRUETM

DuraTRUE 90[™]

UltraTRUE[™]

UltraTRUE 90TM

EverTRUETM

EQ Series



Cost-effective and flexible thanks to the modular RediMount™ motor mounting system

Low-backlash planetary gearhead

Precise, compact and low maintenance thanks to TRUE planetary™ gearing

Low-backlash planetary gearhead

Up to 98% efficiency with the PowerTRUE™ right-angle gearing

Low-backlash right-angle planetary gearhead

Optimum smooth running characteristics, torque capacity and precision thanks to crowned helical gearing

Low-backlash planetary gearhead

One of the quietest and smoothest right-angle planetary gearheads on the market Low-backlash right-angle planetary gearhead

Rigorous design concept to ensure a service life of at least 30,000 hours in continuous operation Low-backlash planetary gearhead

Low noise and low vibration thanks to patented "Swing Link" technology

Planetary gearhead

Let us provide a unique solution for your specific gearhead requirements Customised gearhead solutions

	NemaTRUE™ DuraTRUE™		DuraTRUE 90™			UltraTRUE™	UltraTRUE 90™	EverTRUE™	EQ Series
Torque capacity [Nm] up to	180	834	842	865	865	3300	3111	1010	29
Ratio $ \begin{array}{ll} \mbox{min. i =} \\ \mbox{max. i =} \end{array} $	3 100	3 100	1 500	1 500	1 500	4 100	1 50	4 100	3 100
Radial load capacity [N] up to	3730	11150	11150	11150	11150	37910	37778	44600	1516
Mounting Form									
Right angle			•	•	•		•		
In-line	•	•				•		•	•
Torsional Backlash									
≤ 4 arcmin						•	•	•	
≤8 arcmin	•	•	•	•	•				
≤ 13 arcmin	•								
≤ 18 arcmin									•
Input Form									
Motor mounting	•	•	•	•	•	•	•	•	•
RediMount [™] system	•	•	•	•	•	•	•	•	•
Output Form									
Single shaft	•	•	•			•	•	•	•
Dual shaft					•				
Hollow shaft				•					
Gearing									
TRUE planetary™ gearing	•	•	•	•	•			•	•
Helical crowned gearing						•	•		
PowerTRUE™ right angle gearing			•	•	•		•		
Frame Size									
60	•	•	•		•	•	•		•
75						•	•		
90	•	•	•	•	•	•	•		
100						•	•	•	
115	•	•	•	•	•	•	•		
140						•	•	•	
142		•	•	•	•				
180						•	•	•	


www.thomsonlinear.com 03

TRUE Planetary™ Gearheads

for high precision motion control applications which require a high torque to volume ratio, high torsonial stiffness and low backlash.

- · High torque to size ratio allows compact design
- Low backlash eliminates positioning errors due to lost motion
- Inertia matching keeps servo system stable and in control
- · High rigidity optimizes system response
- Self re-lubrication eliminates costly maintenance and downtime
- · High radial load capacity mount pulleys and pinions directly on the output shaft

- 1 Output shaft
- Tapered roller bearings provide high axial and radial load carrying capacity
- 3 Anodized aluminum housing (DuraTRUE™)
 Stainless steel housing (UltraTRUE™, EverTRUE™)
- 4 HRC 55-60 steel gears provide superior wear resistance and increased backlash integrity
- 5 Sealed deep groove ball bearing provides high radial load carrying capability
- 6 RediMount™ system provides error-free motor installation



Custom Engineered Solutions developed in close cooperation with you.

- · Concept to prototype within weeks
- Compact integrated servo-actuator solutions
- Precision gearing to AGMA 14 standards
- ISO 9001 certified with in-house product testing and fully accredited metallurgical lab









Helical Crowned TRUE Planetary™ Gearheads

combine the positive attributes of gear crowning and helical gearing with the planetary construction to create the smoothest operating gearhead on the market.

- High Torque Capacity
- Low Backlash
- · Smooth Operation
- · Greater Load Sharing
- Whisper Quiet

Helical gears are known for their quiet and smooth operation along with their ability to transmit higher loads than spur gears.

Crowning is a modification to the gear tooth profile which optimizes gear mesh alignment. It also enhances distribution of loading on the tooth flank, thereby reducing high stress regions which can result in surface pitting.

Spur vs. helical gearing


The Contact ratio is defined as the number of teeth in mesh at any given time. The higher the contact ratio, the higher the torque rating of the gearing. Helical gearing has more than 2x the contact ratio of spur gearing.


Crowned vs. non-crowned

Crowning optimizes the gear mesh alignment within a gear train to increase the torque capacity and reduce noise. It also enhances load distribution on the tooth flank to reduce high stress regions.



UltraTRUE in-line planetary[™] gearhead with helical gearing






www.thomsonlinear.com 05

TRUE Planetary™ Gearheads

for high precision motion control applications which require a high torque to volume ratio, high torsonial stiffness and low backlash.

- · High torque to size ratio allows compact design
- Low backlash eliminates positioning errors due to lost motion
- Inertia matching keeps servo system stable and in control
- · High rigidity optimizes system response
- Self re-lubrication eliminates costly maintenance and downtime
- High radial load capacity mount pulleys and pinions directly on the output shaft
- 1 Output shaft
- 2 Anodized aluminum housing (DuraTRUE[™])
 Stainless steel housing (UltraTRUE[™], EverTRUE[™])
- 3 HRC 55-60 steel gears provide superior wear resistance and increased backlash integrity
- 4 Innovative PowerTRUE[™] gearing delivers smooth, quiet geared reduction
- 5 RediMount[™] hub provides error-free motor installation
- 6 RediMount[™] input housing provides error-free motor installation






PowerTRUE[™] right angle gearset



CNC machining of a PowerTRUE™ right angle gear



Computerized mapping of gear tooth profile

RediMount™ Motor Mounting System


allows an easy, error free and quick connection of our Micron gearheads to any current motor in the market. The innovative design with adapter sleeve and input housing features mounting the Micron gearhead within one working process.

- · Self-aligning hub Maintains concentricity between motor shaft and gearhead
- Pre-installed pinion Eliminates pinion setting procedure
- Modular design Allows gearhead and input housing to be stocked separately
- Flexibility Allows easy changeover to alternate motors
- Interchangeability Same RediMountTM system is used throughout 7 product lines

RediMount[™] offers an easy and error free connection between motor and gearhead in only a few minutes:

- 1. Slide the supplied sleeve into the gearhead hub.
- 2. Slide the gearhead hub onto the motor shaft.
- 3. Tighten the hub bolts through the assembly holes of the input housing.
- 4. Bolt the motor to the gearhead with the bolts provided.







USA, CANADA and MEXICO

Thomson

203A West Rock Road Radford, VA 24141, USA Phone: 1-540-633-3549 Fax: 1-540-633-0294

E-mail: thomson@thomsonlinear.com Literature: literature.thomsonlinear.com

EUROPE

United Kingdom

Thomson Office 9, The Barns Caddsdown Business Park Bideford

Devon, EX39 3BT

Phone: +44 (0) 1271 334 500

E-mail: sales.uk@thomsonlinear.com

Germany

Thomson

Nürtinger Straße 70 72649 Wolfschlugen Phone: +49 (0) 7022 504 0 Fax: +49 (0) 7022 504 405

E-mail: sales.germany@thomsonlinear.com

France

Thomson

Phone: +33 (0) 243 50 03 30 Fax: +33 (0) 243 50 03 39

 $\hbox{E-mail: sales.france@thomsonlinear.com}$

Italy

Thomson Largo Brughetti 20030 Bovisio Masciago Phone: +39 0362 594260 Fax: +39 0362 594263

E-mail: sales.italy@thomsonlinear.com

Spain

Thomson

E-mail: sales.esm@thomsonlinear.com

Sweden

Thomson Estridsväg 10 29109 Kristianstad Phone: +46 (0) 44 24 67 00 Fax: +46 (0) 44 24 40 85

E-mail: sales.scandinavia@thomsonlinear.com

ASIA

Asia Pacific

Thomson

E-mail: sales.apac@thomsonlinear.com

China

Thomson

Rm 2205, Scitech Tower 22 Jianguomen Wai Street

Beijing 100004

Phone: +86 400 6661 802 Fax: +86 10 6515 0263

E-mail: sales.china@thomsonlinear.com

India

Thomson

c/o Fluke Technologies Pvt. Ltd.

#424, Deodhar Center, Marol Maroshi Road,

Andheri - E, Mumbai - 400059 India

Phone: +91 22 29207641

E-mail: sales.india@thomsonlinear.com

Japan

Thomson

Minami-Kaneden 2-12-23, Suita Osaka 564-0044 Japan Phone: +81-6-6386-8001 Fax: +81-6-6386-5022 E-mail: csjapan@scgap.com

Korea

Thomson

F7 Ilsong Bldg, 157-37 Samsung-dong, Kangnam-gu, Seoul, Korea (135-090) Phone: +82 2 6917 5049 Fax: +82 2 528 1456

E-mail: sales.korea@thomsonliear.com

SOUTH AMERICA

Brazil

Thomson Av. Tamboré, 1077 Barueri, SP – 06460-000

Phone: +55 (11) 3616-0191 Fax: +55 (11) 3611-1982

E-mail: sales.brasil@thomsonlinear.com

