

T-Series Ball Profile Rail


TECHNICAL BULLETIN




www.thomsonlinear.com



T-Series Profile Rail





Note: 1. Sold as assemblies only

2. Carriages are dimensionally matched to rails during assembly

T-Series Ball Profile Rail

Features

The Thomson T-Series Ball Profile Rail is lightweight, highly flexible and forgiving — an ideal choice for poor misalignment. It has a low cost of installation and industry standard dimensions for easy replacement. It is a lightweight and forgiving alternative to all-steel profile rail.

Materials

The Thomson T-Series Ball Profile Rail carriage and rail is produced from high quality aircraft aluminum alloy. The carriage has hardened steel load bearing plates. The rail has a custom ball path insert made of hardened steel. Stringent quality controls are in place to ensure consistency of steel from the source, allowing us to ensure that we deliver the highest quality product.

Lightweight

The aluminum carriage and rail dramatically reduces the total weight of the assembly making Thomson T-Series an ideal choice for applications requiring reduced weight inertia such as airplanes, ships, automobiles, etc.

Accuracy

As a result of it's high flexibility to misalignment errors, the T-Series Ball Profile Rail is available in an N class radial run out only.

Forgiving to Misalignment


The Thomson T-Series propriety "U" channel construction allows the rail to "flex" to accommodate poor machine bases or misalignment errors.


Low Cost

The Thomson T-Series can be mounted direct to non-machined bases without sacrificing total operational efficiency or the need for special tools or gauges to ensure proper rail and base straightness. By eliminating the costly machined base and special tools the installation time or machine build time can be cut in half, saving valuable time and money.


Drop-in Replacement

The Thomson T-Series is designed to industry standard dimensions and rail hole patterns. This means it can be used as a drop-in replacement for any conventional all steel profile linear guide in the market today.







T-Series Carriage Styles



T-Series Style A and G








t- Will be equal on both ends, unless otherwise specified.

Supplied Lubrication Fittings



T-Series Profile Rail Standard High "A" Style

Size	Α	A1	A2	A3	н	H1	H2	В	E1	E2	S1	S2	S 3	S5	S6	N1	N5	N6	Х	L _{max}
20	63	31.5	20	21.5	30	25	18	76	53	40	M5	M6	M5	5.8	9.5	10	6.25	7,5	60	3000
25	70	35	23	23.5	36	29.5	22	88	57	45	M6	M8	M6	7	10.7	12	8	10	60	3000
35	100	50	34	33	48	40	29	117	82	62	M8	M10	M8	9	14	15.26	6.6	11	80	3000

All dimensions in mm unless shown otherwise

T-Series Profile Rail Standard "G" Style

Size	A	A1	A2	A3	н	H1	H2	В	E1	E2	S1	S2	S 3	S5	S6	N1	N5	N6	Х	L _{max}
20	59	29.5	20	19.5	28	23	18	76	49	32	M5	M6	M5	5.8	9.5	8	4.25	7.5	60	3000
25	73	36.5	23	25	33	26.5	22	88	60	35	M6	M8	M6	7	10.7	9	5	10	60	3000
35	100	50	34	33	48	40	29	117	82	50	M8	M10	M8	9	14	15.26	6.6	11	80	3000

T-Series Style A and G

Dynamic Load Rating


C = Dynamic load rating

The dynamic load rating is based upon a 100 km travel life. In order to compare with bearings rated for 50 km, divide the dynamic rating of the bearing rated for 50 km by 1.26.

Static Load Capacity

C₀ = Static load capacity

The static load capacity is the maximum radial load that should be applied to the bearing while there is no relative motion between the carriage and rail.



		Load Rat	Load Ratings N (lbf)						
Size	Style	C (@100km)	Co	Carriage kg	Rail kg/m				
20	A G	9000 (2025)	11000 (2475)	0.22	0.79				
25	A G	13000 (2925)	15000 (3375)	0.30	1.06				
35	A G	25000 (5620)	28000 (6295)	0.74	2.27				

	Dynamic Load Rating	Load Limit
F _c	C	C
Ft	C	0.6C
Fs	С	0.6C


Bearing Travel Life Calculation

L = (C/F)³ x 100 km where: L = travel life, km C = dynamic load rating, N F = applied dynamic load, N

Operating Parameters

Maximum Velocity = 3 m/s Maximum Acceleration = 50 m/s2 Maximum Temperature = 80°C

T-Series Style E and F



T-Series Profile Rail Narrow "E" Style

Size	Α	A1	A2	A3	A4	Н	H1	H2	В	E1	E2	S 2	S3	S5	S6	N3	N5	N6	Х	L _{max}
20	44	22	20	12	41.5	30	25	18	76	32	36	M5	M5	5.8	9.5	6	6.25	7.5	60	3000
25	48	24	23	12.5	50.9	40	33.5	22	88	35	35	M6	M6	7	10.7	8	12	10	60	3000
35	70	35	34	18	68.0	55	47	29	117	50	50	M8	M8	9	14	12	13.6	11	80	3000

All dimensions in mm unless shown otherwise

T-Series Profile Rail Narrow High "F" Style

Size	Α	A1	A2	A3	A4	Н	H1	H2	В	E1	E2	S2	S3	S5	S6	N3	N5	N6	Х	L _{max}
20	42	21	20	11	41.5	28	23	18	76	32	32	M5	M5	5.8	9.5	6	4.25	7.5	60	3000
25	48	24	23	12.5	51.0	33	26.5	22	88	35	35	M6	M6	7	10.7	8	5	10	60	3000
35	70	35	34	18	68.0	48	40	29	117	50	50	M8	M8	9	14	12	6.6	11	80	3000

All dimensions in mm unless shown otherwise

T-Series Style E and F

Dynamic Load Rating


C = Dynamic load rating

The dynamic load rating is based upon a 100 km travel life. In order to compare with bearings rated for 50 km, divide the dynamic rating of the bearing rated for 50 km by 1.26.

Static Load Capacity

C₀ = Static load capacity

The static load capacity is the maximum radial load that should be applied to the bearing while there is no relative motion between the carriage and rail.



		Load Rat	Load Ratings N (lbf)						
Size	Style	C (@100km)	Co	Carriage kg	Rail kg/m				
20	A G	9000 (2025)	11000 (2475)	0.22	0.79				
25	A G	13000 (2925)	15000 (3375)	0.30	1.06				
35	A G	25000 (5620)	28000 (6295)	0.74	2.27				

	Dynamic Load Rating	Load Limit
F _c	C	C
Ft	C	0.6C
Fs	С	0.6C

Bearing Travel Life Calculation

L = (C/F)³ x 100 km where: L = travel life, km C = dynamic load rating, N F = applied dynamic load, N

Operating Parameters

Maximum Velocity = 3 m/s Maximum Acceleration = 50 m/s2 Maximum Temperature = 80°C

USA, CANADA and MEXICO

Thomson 203A West Rock Road Radford, VA 24141, USA Phone: 1-540-633-3549 Fax: 1-540-633-0294 E-mail: thomson@thomsonlinear.com Literature: literature.thomsonlinear.com

EUROPE

United Kingdom Thomson Office 9, The Barns Caddsdown Business Park Bideford, Devon, EX39 3BT Phone: +44 (0) 1271 334 500 E-mail: sales.uk@thomsonlinear.com

Germany

Thomson Nürtinger Straße 70 72649 Wolfschlugen Phone: +49 (0) 7022 504 403 Fax: +49 (0) 7022 504 405 E-mail: sales.germany@thomsonlinear.com

France

Thomson Phone: +33 (0) 243 50 03 30 Fax: +33 (0) 243 50 03 39 E-mail: sales.france@thomsonlinear.com

Italy

Thomson Via per Cinisello 95/97 20834 Nova Milanese (MB) Phone: +39 0362 366406 Fax: +39 0362 276790 E-mail: sales.italy@thomsonlinear.com

Spain

Thomson E-mail: sales.esm@thomsonlinear.com

Sweden

Thomson Estridsväg 10 29109 Kristianstad Phone: +46 (0) 44 24 67 00 Fax: +46 (0) 44 24 40 85 E-mail: sales.scandinavia@thomsonlinear.com

ASIA

Asia Pacific Thomson E-mail: sales.apac@thomsonlinear.com

China

Thomson Rm 2205, Scitech Tower 22 Jianguomen Wai Street Beijing 100004 Phone: +86 400 6661 802 Fax: +86 10 6515 0263 E-mail: sales.china@thomsonlinear.com

India

Thomson c/o Fortive India Pvt. Ltd. Unit No. FF A 07 Art Guild House, A Wing, 1st Floor, L.B.S Marg Kurla – West, Mumbai – 400070 India Phone: +91 22 6249 5043 E-mail: sales.india@thomsonlinear.com

Japan

Thomson Minami-Kaneden 2-12-23, Suita Osaka 564-0044 Japan Phone: +81-6-6386-8001 Fax: +81-6-6386-5022 E-mail: csjapan@scgap.com

Korea

Thomson ROA 704 ASEM Tower (Samsung-dong), 517 Yeongdong-daero, Gangnam-gu, Seoul, S. Korea (06164) Phone: +82 2 6917 5047 / 5048 Fax: +82 2 528 1456 / 1457 E-mail: sales.korea@thomsonlinear.com

SOUTH AMERICA

Brasil

Thomson Av. Tamboré, 1077 Barueri, SP – 06460-000 Phone: +55 (11) 3616-0191 Fax: +55 (11) 3611-1982 E-mail: sales.brasil@thomsonlinear.com

www.thomsonlinear.com

200606-01 | 20191016TJ

Specifications are subject to change without notice. It is the responsibility of the product user to determine the suitability of this product for a specific application. All trademarks property of their respective owners. © 2019 Thomson Industries, Inc.



Linear Motion. **Optimized.**™