

Miniature Components and Systems Superior Performance, Precision and Reliability – in Miniature Form



Miniature Machine Components Engineered to Work Together

Thomson produces the widest selection of miniature linear motion components that are engineered to work side by side seamlessly. This cohesive approach equates to faster design times, less installation problems, and higher performance and reliability.

The Thomson family of miniature products provides linear thrust and guidance motion control in the smallest packages available. They all benefit from our vast experience in motion control engineering, and have all the advantages and features offered for standard-sized products.

Thomson also provides customized solutions. Whether you need alternative materials, nut geometry, configured bearings, special end machining or mounting features, we have the solution.

The Thomson Advantage

Smaller components enable designers to reduce the size and weight of their end product, resulting in products that are smaller, lighter and less expensive to produce. A smaller product will also reduce packaging and transportation cost, while lessening the overall environmental impact of the equipment. Choosing Thomson as your supplier carries additional advantages as well.

	Thomson Advantages	
	Advantage	Benefits
00	Widest variety of miniature linear products on the market	Expedited design timeSingle source of engineering supportConsolidated supply base
	Products designed to work together	Online sizing and selection tools for easy designFewer installation problemsHigher-performance equipment
	Easy customization	Custom sizes, finishes, materials and moreOptimized cost, size and performance
	Genuine Thomson quality	Fewer defects and field failuresLower overall cost of ownership
	Global company	Sales and support around the globeSafe partner with proven track recordKnowledge about local standards and preferences

F


Miniature Components and Systems Overview

Products providing thrust

Products providing guidance

Products providing both thrust and guidance

Linear Motion Miniature Products Overview*								
Product Image	Product Group	Product Line Name (Product Suffix)	See Page	Basic Specifications				
		Miniature Lead Screw	8	2 – 4 mm				
		Lead Screw and Flange Mount Supernut (MTS)	8	6 – 20 mm 3/16 – 3/4 in.				
	Lead Screws	Lead Screw and Anti-Backlash Supernut (AFT)	8	10 mm 3/8 — 1/2 in.				
		Lead Screw and Anti-Backlash Supernut (XC)	8	6 – 24 mm 3/16 – 1 in.				
	Ball Screws	Miniature Metric - Flanged Miniature Metric - Threaded Miniature Metric - Cylindrical	9	8 – 12 mm				
	Ball Splines	Precision Ball Splines	10					
		60 Case [®] LinearRace [®] Shafting and Miniature Instrument Bearing (INST)	11	1/8 — 1/4 in.				
S	Linear Bearings	60 Case LinearRace Shafting and Polymer Bushing Bearing (PL)	11					
		60 Case LinearRace Shafting and Super Ball Bushing Bearing (SP)	11	12 — 40 mm 1/2 — 1-1/2 in.				
· · · · · · · · · · · · · · · · · · ·	Profile Rail	Microguide™ (TSR)	12	5 – 15 mm				
	Glide Screws	Glide Screw™ (GS)	13	4 — 10 mm 3/16 — 3/8 in.				
	Stepper Motor Linear Actuators	Motorized Lead Screws (MLS) Motorized Lead Nuts (MLN) Motorized Lead Screw Actuators (MLA)	14					
	Compact Linear Systems	Narrow/Vertical Configuration (CLSV) Wide/Horizontal Configuration (CLSH) Round Rail Configuration (CLSR)	15					




* These are a small selection from our standard product ranges. More product ranges are available, and most products also come in additional sizes and versions. Thomson specializes in making customized products to meet your exact specifications. See page 17 for more information.

Unit of N	<i>Aeasure</i>	Anti-backlash or Preload	No or Low Maintenance	Noise Level	Product Cost	Stiffness Properties	Accuracy	Corrosion	Thrust	Guidance
Metric	Inch	Feature	Required	Levei	Level	Froperties	roperties	Resistance Properties	Capacity Level	Capacity Level
•		•	•	* * *	* * *	*	*	* * *	*	
•	•		•	***	***	*	*	***	**	-
•	•	•	•	***	**	*	**	***	*	-
•	•	•	•	***	**	*	**	***	**	-
•		•		*	**	*	* * *	*	* * *	-
٠		•		**	**	**	$\star \star \star$	$\star \star$	-	$\star \star$
	•			**	*	**	***	***	-	*
•			•	$\star \star \star$	**	*	★	$\star \star \star$	-	*
•	•	•		**	* * *	*	**	**	-	**
•		•		**	**	***	***	***	-	$\star \star \star$
•	•		•	* * *	**	★	*	***	**	**
•	•	•	•	**	**	*	*	**	**	★ MLA only
•		•	•	**	$\star\star$	*	$\star \star$	*	**	**



Applications

Miniature linear motion components are ideal for applications where precise movement of small loads is critical. In particular, they add value in instruments for medical diagnostics, test and measurement equipment, and engraving and printing, as well as a broad range of fluid pumping and pick-and-place applications.



Applications

Test and Measurement Equipment

- Torque testers
- Load and pull testers

Design iterations for testing and

measurement devices allow for

easier use, better quality and faster

results. One example is a smaller

footprint found in the handheld

ear scanning device shown here. Smaller devices like this can benefit from Thomson miniature lead screws in their design

application.

Handheld devices



Thomson precision ball splines simplify XYZ movement into linear and rotary motion, thereby reducing the number of parts and complexity required for picking up an item and placing it in another location. Fewer components and simpler designs result in lower costs, higher efficiencies, less maintenance and quicker lead times.

Robotics and Pick & Place Equipment

- Engraving, scanning and printing machines
- Electronics manufacturing equipment
- Medical surgery manipulators/robots
- Manipulators for use in hazardous areas
- Camera inspection equipment

Thomson provides custom sizes, finishes and materials for engraving/printing machines to deliver an optimized solution. In this example, utilizing a stepper motor linear actuator on a 3D printer eliminates the need for couplings, bearings and supports while increasing stroke length and print volume.

Motorized Lead Screws

Precision Ball Spline

Other Applications

- Portable installations (e.g. bedside scanner)
- Portable ventilators
- Dosage equipment
- Electronics manufacturing equipment
- Inspection, scanning and printing equipment
- Packaging and dispensing equipment
- Aerospace and defense applications
- Vending machines



Lead Screws

Lead Screws and Supernuts (MTS, AFT and XC) Miniature Lead Screws and Nuts



Main Features

Lead Screws

- Lead accuracy up to 0.003 in./ft. (75 $\mu\text{m}/300$ mm)
- Highly customizable solutions for OEM applications
- Precision screw machining
- Optional materials and coatings available

Supernut MTS

- Excellent lubricity and dimensional stability
- Cost-effective manufacturing, including integral flange

Supernut AFT

- Designed for light-load applications
- Offers smooth movement and low drag torque
- Anti-backlash adjusts for wear for the life of the nut

Supernut XC

- Utilizes Thomson patented ActiveCAM technology
- Offers low drag torque and high axial stiffness
- Anti-backlash ensures consistent performance and repeatability

Miniature Lead Screws

- Diameters as small as 2 mm
- Optional anti-backlash design
- Customizable end machining, special coatings, unique nut design and end configurations
- Patent-pending integrated coupler for easy mounting

Performance Specifications						
Product Line			Lead Screws			
Model		MTS	AFT	XC	Miniature	
Screw diameter range metric version inch version	[mm] [in.]	6 – 20 3/16 – 3/4	10 3/8 – 1/2	6 - 24 3/16 - 1	2-4	
Lead range metric version inch version	[mm] [in.]	1 — 50 0.031 — 2.000	2 - 20 0.050 - 1.200	1 — 50 0.050 — 2.000	0.375 – 8	
Backlash	[mm]	< 0.254	0	0	0.064 max / 0.0 min	
Axial design load, maximum	[N]	1225	110	1560	44	
Accuracy, standard rolled (precision rolled)	Supernut: [µm/300 mm] Lead Screws: [mm/mm]		0.0005			
Maintenance			Designed to minimize pr	reventative maintenance		

Ball Screws

Miniature Metric Ball Screws (Rolled/Ground)



Main Features

- Design maximizes load capacity
- Quiet and smooth performance
- Flexible ball nut mounting configurations and rapid prototyping
- Exceeds 100% more capacity than competition in most sizes
- Higher load capacity equates to longer life
- Precision ball screws to P5 accuracy class

Performance Specifications							
Product Line			Min	iature, metric, rolled/gro	ound		
Screw diameter, nominal	[mm]	8	8	10	10	12	
Lead	[mm]	2,5	5	2	3	2	
Nut size (diameter × length)	[mm]	ø 16 x 18	ø 16 x 23	ø 19 × 24	ø 19 × 29	ø 24 × 34	
Dynamic load capacity (1)*	[kN]	2.1	2.5	3.7	5.2	5.9	
Static load capacity*	[kN]	2.2	2.8	4.6	6.9	8.9	
Ball diameter	[mm]	1.588	1.588	1.588	1.588	1.588	
Length of screw, maximum	[mm]	280	280	3000	3000	3000	
Axial backlash, maximum	0.05	0.05	0.05	0.05	0.05		
Material		Carbon Stee	I - AISI 1566	Carbon Steel - CF53			
Maintenance		High load density ensures maximum life					

(1) Based on one million revolutions.

* Load rating calculations comply with ISO 3408-5.



Ball Splines Precision Ball Splines



Main Features

- Nearly friction-free linear and rotary motion integrated on a single shaft
- · Wide, precision-ground grooves allow for increased load-carrying capabilities
- Improved rigidity and stiffness for handling larger moment loads
- Groove design similar to Gothic arches allows for zero angular clearance and backlash
- A 40° angular contact allows grooves to operate with minimal friction, while achieving optimal sensitivity
- Simple, ball-retaining design allows for mess-free removal of the spline nut

Performance Specifications						
Product Line			Precision Ball Splines			
Spline diameter, nominal*	[mm]	6	6 8 10			
Overall length	[mm]	50	500 3000			
Accuracy		Normal				
Precision	[µm]	136				
Mounting			Flanged, Round			
Shaft type			Solid			
Spline material		S55C/SUJ2				
Nut material		SCM415H				
Number of grooves		2				

* Larger diameter sizes are available.

Linear Bearings

60 Case[®] LinearRace[®] Shafting and Linear Ball Bushing[®] Bearings (INST, SP and PL)



Main Features

60 Case LinearRace Shafting

- Manufactured to the highest quality standards
- Different materials, surface treatments and special machining available

Miniature Instrument Bearing (INST)

- High accuracy and responsiveness
- For smaller loads

Super Ball Bushing Bearing (SP)

- · Low cost, easy to install and long life
- · Industry standard for self-aligning linear bearings

Polymer Bushing Bearing (PL)

- Maintenance-free operation
- Polymer liners reduce noise
- Dirt and dust resistant
- Anodized aluminum adapter

Performance Specifications					
Product Line		Miniature Instrument (INST)			Polymer Bushing Bearing (PL)
Unit of measure version		Inch	Metric	Inch	Metric
Shafting size range metric version inch version	[mm] [in.]	- 1/8 — 1/4	12 - 40	- 1/2 — 1-1/2	6 – 50 (closed) -
Dynamic bearing load, maximum metric version inch version	[N] [lbf]	84	14700	- 3000	9000
Linear speed, maximum	[m/s]		3		8
Friction coefficient			0.001 - 0.004		
Bearing material (standard configuration)		440 stainless steel	Carbon stee	el and delrin	Anodized aluminum
Maintenance			Light lul	brication	

Bearing

Profile Rail Guides Microguide™ (TSR)



Main Features

- Low profile
- Available in standard and wide profile styles
- Available in H and P accuracy classes
- Quiet and smooth operation
- Low weight
- Industry standard, drop-in replacement
- High moment load capacity
- Two-track, gothic-arch ball groove geometry enables single rail application

Performance Specifications										
Product Line						Microguide				
Model		TSR5Z	TSR7Z	TSR7ZW	TSR9Z	TSR9ZW	TSR12Z	TSR12ZW	TSR15Z	TSR15ZW
Size of carriage and rail (W \times H)	[mm]	6×12	8 × 17	9×25	10 × 20	12 × 30	13 × 27	14×40	16 × 32	16 × 60
Rail length, minimum/maximum	[mm]	40/160	40/1000	50/1010	55/1015	50/1010	70/1020	70/1030	150/1030	110/1030
Dynamic load, maximum	[N]	336	924	1370	1544	2450	2780	4020	4410	6660
Linear speed, maximum	[m/s]					3				
Acceleration, maximum	[m/s ²]					50				
Accuracy	[± mm]	up to 0.01								
Material	[kg/m]	440 stainless steel								
Maintenance					Lię	ght lubricati	on			

Glide Screws Glide Screw™ (GS)



Main Features

- Lead screw and linear bearing combined
- Patented design
- Aligned from factory
- Side load and moment load capable
- Integrated lubrication block no maintenance requried
- Smooth and quiet motion
- Cylindrical or flanged nuts available
- Versions for high temperature, clean room and food grade applications available

Performance Specifications						
Product Line			Glide	Screw		
Model	GS4	GS6	GS10	GS18	GS25	GS37
Screw diametermetric version[mm]inch version[in.]	4 -	6 -	10 -	- 0.188	- 0.250	- 0.375
Screw lead metric version [mm] inch version [in.]	1, 4, 8	1, 6, 12 -	2, 6, 12	- 0.05, 0.125	- 0.05, 0.5, 0.75	- 0.063, 0.5, 1
Screw length, maximummetric version[mm]inch version[in.]	150 -	250	450	- 6	- 10	- 18
Axial load, maximum metric version [N] inch version [Ibs]	89.0	133.4	311.4	- 30	- 45	- 70
Moment load, maximummetric version[Nm]inch version[in-lbs]		5.4	15.5 -	- 20.5	- 47.5	- 137.5
Maintenance	Maintenance free					

₿ I

Stepper Motor Linear Actuators

Motorized Lead Screw (MLS), Motorized Lead Nut (MLN) and Motorized Lead Screw Actuator (MLA)



Main Features

- Increased torque density by up to 30% while maintaining the same motor footprint
- Improved efficiency with reduced power consumption, better battery life and decreased motor footprint
- Rotating screw, rotating nut or actuator
- Custom sizes/leads available
- Taper-Lock design provides a secure, self-aligning connection between the lead screw and stepper motor
- Reduced noise
- Inch or metric versions

Performance Specifications							
Lead Screw	Lead Screw						
Material			300) Series Stainless S	teel		
Standard lead accuracy	[in./ft. (µm/300 mm)]		0.010 (250)				
Precision lead accuracy	[in./ft. (µm/300 mm)]		0.003 (75)				
Lead Nut	Lead Nut						
Standard material			Interna	Ily lubricated aceta	I (POM)		
Typical linear travel life	[in. (km)]			5 x 10 ⁶ (125)			
Motor							
Frame size		NEMA 8	NEMA 11	NEMA 14	NEMA 17	NEMA 23	
Step size	[°]			1.8			
Max. axial load	[lbs. (N)]	5 (22)	20 (89)	50 (222)	75 (334)	200 (890)	
Axial pre-load	[lbs. (N)]	5 (22)	20 (89)	30 (133)	40 (178)	40 (178)	

Compact Linear Systems Narrow (CLSV), Wide (CLSH), Round Rail (CLSR)



Main Features

- Choose from three standard architectures or build a "from scratch" system
- Mounting blocks can be machined to virtually any shape or size
- Virtual design consultations are like having a linear motion expert by your side as you build your solution
- Systems can be produced and delivered quickly due to back-end modularity processes being automated
- A 3D model of your system is made available to you in real time or typically within one business day

Performance Specifications							
Lead Screw	Lead Screw						
Material			300 Series Stainless Steel				
Standard lead accuracy	[in./ft. (µm/300 mm)]		0.010 (250)				
Precision lead accuracy	[in./ft. (µm/300 mm)]		0.003 (75)				
Lead Nut							
Standard material		I	nternally lubricated acetal (PON	1)			
Typical linear travel life	[in. (km)]		10 x 10 ⁶ (250)				
Motor							
Frame Size		NEMA 14	NEMA 17	NEMA 23			
Step size	[°]		1.8				
Axial pre-load	[lbs. (N)]	30 (133)	40 (178)	40 (178)			
Assembly							
Max. backlash with standard nut	[in. (mm)]		0.010 (0.25)				

www.thomsonlinear.com



Customization

Applications often have unique challenges that cannot always be solved by an off-the-shelf solution. Thomson specializes in providing custom-engineered solutions quickly and cost effectively to address these requirements.



Thomson has proven that custom designs can offer optimum performance at a low overall cost. 3D CAD design, rapid prototyping and flexible manufacturing have made customization a faster process. Once the product is ready and approved, it will be manufactured and shipped as quickly as a standard product.


Selection of Customization P	ossibilities
Type of customization	Examples
Custom materials	 Stainless steel bearings or an aluminium/plastic housing Nuts or bushings made in a special metal, plastic, composite or ceramic material Replacement of hardware to meet demands in special environments
Custom surface treatment	 Paint of different quality and/or color Thicker anodization on aluminum parts Specially coated screws or sliding surfaces (PTFE, chrome, black oxide, etc.)
Custom size or geometry	 Non-standard stroke lengths Custom end machining or motor/mounting interfaces Special nut, carriage or flange designs
Custom assemblies	 Product shipped with mounting brackets, gearboxes and/or motors mounted Product shipped in parts or sub-assemblies for the customer to assemble Product shipped mounted to the customer's equipment
Custom services	 Special lubrication Special stocking or transportation program Training of engineers, maintenance or other personnel Special service, repair and/or maintenance program Special packaging, testing, certification or quality control procedures Engineering evaluation
New designs	Change or combine one or several products into a new productClean sheet designs

Online Resources

Thomson offers a wide variety of online application, selection and training tools to help you. An experienced team of application engineers is also available to help size and select a miniature component to best fit your needs. To explore additional technical resources and options, contact Thomson customer support at www.thomsonlinear.com/contact.

Linear Components on the Web

Find additional information and learn more about Thomson miniature components and systems throughout our content-rich website. www.thomsonlinear.com




Selector Tools

These tools greatly simplify the tasks of searching and selecting with a visual selection process that immediately narrows down your component options. www.thomsonlinear.com/en/design-tools/thomsonselectors



Interactive 3D CAD Models

Download free interactive 3D models in the most common CAD formats. www.thomsonlinear.com/en/ design-tools/thomson-models





Notes

	Miniature Components & Systems
Notes	

USA, CANADA and MEXICO

Thomson 203A West Rock Road Radford, VA 24141, USA Phone: 1-540-633-3549 Fax: 1-540-633-0294 E-mail: thomson@regalrexnord.com Literature: literature.thomsonlinear.com

EUROPE

United Kingdom

Thomson Office 9, The Barns Caddsdown Business Park Bideford, Devon, EX39 3BT Phone: +44 1271 334 500 E-mail: thomson.europe@regalrexnord.com

Germany

Thomson Nürtinger Straße 70 72649 Wolfschlugen Phone: +49 7022 504 403 Fax: +49 7022 504 405 E-mail: thomson.europe@regalrexnord.com

France

Thomson Phone: +33 243 50 03 30 E-mail: thomson.europe@regalrexnord.com

Italy

Thomson Via per Cinisello 95/97 20834 Nova Milanese (MB) Phone: +39 0362 366406 Fax: +39 0362 276790 E-mail: thomson.italy@regalrexnord.com

Sweden

Thomson Bredbandsvägen 12 29162 Kristianstad Phone: +46 44 590 2400 Fax: +46 44 590 2585 E-mail: thomson.europe@regalrexnord.com

ASIA

Asia Pacific Thomson E-mail: thomson.apac@regalrexnord.com

China

Thomson Rm 805, Scitech Tower 22 Jianguomen Wai Street Beijing 100004 Phone: +86 400 606 1805 Fax: +86 10 6515 0263 E-mail: thomson.china@regalrexnord.com

India

Kollmorgen – Div. of Altra Industrial Motion India Private Limited Unit no. 304, Pride Gateway, Opp. D-Mart, Baner Road, Pune, 411045 Maharashtra Phone: +91 20 67349500 E-mail: thomson.india@regalrexnord.com

South Korea

Thomson 3033 ASEM Tower (Samsung-dong) 517 Yeongdong-daero Gangnam-gu, Seoul, South Korea (06164) Phone: + 82 2 6001 3223 & 3244 E-mail: thomson.korea@regalrexnord.com

SOUTH AMERICA

Brazil

Thomson Av. João Paulo Ablas, 2970 Jardim da Glória - Cotia SP - CEP: 06711-250 Phone: +55 11 4615 6300 E-mail: thomson.brasil@regalrexnord.com



www.thomsonlinear.com

A REGAL REXNORD BRAND