

Linear Actuators





12 and 24 Vdc - load up to 75 lbf



Standard Features and Benefits

- Very compact and lightweight
- Integrated end of stroke limit switches
- Corrosion resistant housing
- Self-locking acme screw drive system
- Maintenance free
- Ideal for replacement of comparable size pneumatic and hydraulic cylinders

General Specifications


Parameter	Electrak 1
Screw type	acme
Internally restrained	no
Manual override	no
Dynamic braking	no
Holding brake	no, self-locking
End of stroke protection	end of stroke limit switches
Mid stroke protection	no
Motor protection	auto reset thermal switch
Motor connection	flying leads and connector
Motor connector	Packard Electric Pack-Con male 8911773 with terminal 6294511. Mating connector: 8911772 with terminal 8911639 (p/n 9300-448-001)
Certificates	CE optional*
Options	none

* Contact customer support

Performance Specifications

Parameter		Electrak 1
Maximum load, dynamic / static S •• -09A4 S •• -17A8	[lbf]	25 / 300 75 / 300
Speed, at no load / at maximum load S •• -09A4 S •• -17A8	[in/sec]	3.00 / 2.10 1.00 / 0.65
Available input voltages	[Vdc]	12, 24
Standard stroke lengths	[in]	2, 4, 6
Operating temperature limits	[°F]	-15-+150
Full load duty cycle @ 77 °F	[%]	25
End play, maximum	[in]	0.036
Restraining torque	[lbf-in]	20
Lead cross section	[AWG]	18
Lead length	[in]	4.5
Protection class		IP66

12 and 24 Vdc - load up to 75 lbf



A: retracted length


A1: installation must include at least this much coast beyond limit switch shut off

Ordering stroke	[inch]	2	4	6
Actual stroke (S)	[inch]	1.8	3.8	5.8
Retracted length (A)	[inch]	6.3	8.3	10.3
Weight	[lb]	1.2	1.4	1.5

A3: yellow lead

Performance Diagrams

Life vs. Load




Ncycle: life in number of cycles (one cycle = extend and retract) F max: percent of maximum rated load

1: all models using the internal limit switches for end of stroke


2: all models when end of stroke is controlled externally

Duty Cycle vs. Load



ED: duty cycle in percent at 77° F F max: percent of maximum rated load 1: all models

Speed and Current vs. Load




V: speed I: current F: load 1: speed 25 lbf 2: speed 75 lbf 3: current 25 lbf, 12 Vdc 4: current 25 lbf, 12 Vdc 5: current 75 lbf, 12 Vdc 6: current 75 lbf, 24 Vdc

12 and 24 Vdc - load up to 75 lbf

Ordering Key

5 /		
1	2	3
S24 -	09A4 -	06
1. Model and input voltage S12 - = Electrak 1, 12 Vdc S24 - = Electrak 1, 24 Vdc		3. Stroke 02 = 2 inch 04 = 4 inch 06 = 6 inch

Wiring Diagram



Connect the red lead to positive and yellow to negative to extend the actuator/rotate the output shaft in clockwise direction. Change polarity to retract the actuator/rotate the output shaft counterclockwise. Electrak 1 actuators should be protected from overload conditions by a customer provided fuse in the circuit (6 A for 12 Vdc and 3 A for 24 Vdc).



Electrak 1SP

12 and 24 Vdc - load up to 75 lbf



Standard Features and Benefits

- Very compact and lightweight
- Potentiometer feedback
- Corrosion resistant housing
- Self-locking acme screw drive system
- Maintenance free
- Internally restrained extension tube
- Ideal for replacement of comparable size pneumatic and hydraulic cylinders

General Specifications

Parameter	Electrak 1SP
Screw type	acme
Internally restrained	yes
Manual override	no
Dynamic braking	no
Holding brake	no, self-locking
End of stroke protection	no
Mid stroke protection	no
Motor protection	auto reset thermal switch
Motor connection	flying leads and connector
Motor connector	Packard Electric Pack-Con male 8911773 with terminal 6294511. Mating connector: 8911772 with terminal 8911639 (p/n 9300-448-001)
Certificates	CE optional*
Options	none


* Contact customer support

Performance Specifications

Parameter		Electrak 1SP
Maximum load, dynamic / static SP •• -09A4 SP •• -17A8	[lbf]	25 / 300 75 / 300
Speed, at no load / at maximum load SP •• -09A4 SP •• -17A8	[in/sec]	3.00 / 2.10 1.00 / 0.65
Available input voltages	[Vdc]	12, 24
Standard stroke lengths	[in]	2, 4, 6
Operating temperature limits	[°F]	-15-+150
Full load duty cycle @ 77 °F	[%]	25
End play, maximum	[in]	0.036
Restraining torque	[lbf-in]	0
Lead cross section	[AWG]	18
Lead length	[in]	4.5
Protection class		IP66
Potentiometer	[k0hm]	10**

Electrak 1SP

12 and 24 Vdc - load up to 75 lbf




A1: cable for potentiometer feedback, length = 25 inch

Ordering stroke	[inch]	2	4	6
Actual stroke (S)	[inch]	2.3	4.5	6.8
Retracted length (A)	[inch]	7.8	10.0	12.2
Weight	[lb]	1.2	1.4	1.5
Potentiometer resistance change	[ohm/in]	2400	1200	800

Performance Diagrams


Life vs. Load



Ncycle: life in number of cycles (one cycle = extend and retract) F max: percent of maximum rated load


1: all models when end of stroke is controlled externally

Duty Cycle vs. Load



ED: duty cycle in percent at 77° F F max: percent of maximum rated load 1: all models

Speed and Current vs. Load



V: speed I: current F: load

1: speed 25 lbf 2: speed 75 lbf

3: current 25 lbf, 12 Vdc 4: current 25 lbf, 24 Vdc

5: current 75 lbf, 12 Vdc

6: current 75 lbf, 24 Vdc


Electrak 1SP

12 and 24 Vdc - load up to 75 lbf

Ordering Key

0 7		
1	2	3
SP24 -	09A4 -	06
1. Model and input voltage SP12 - = Electrak 1SP, 12 Vdc SP24 - = Electrak 1SP, 24 Vdc	2. Dynamic load capacity 09A4 - = 25 lbf 17A8 - = 75 lbf	3. Stroke 02 = 2 inch 04 = 4 inch 06 = 6 inch

Electrak 1SP



Connect the black or white* lead to positive and yellow to negative to extend the actuator. Change polarity to retract the actuator. The potentiometer output has 0 ohm between white and red when the actuator is fully retracted. The actuator should be protected from overload conditions by a customer provided fuse in the circuit (6 A for 12 Vdc and 3 A for 24 Vdc).



12, 24 and 36 Vdc - load up to 112 lbf



Standard Features and Benefits

- Designed for office or medical applications
- Small, quiet and lightweight
- Very short retracted length
- Low cost
- Durable and corrosion free plastic housing
- Color molded into the plastic, no painting required
- End of stroke limit switches with dynamic braking
- Maintenance free
- Internally restrained extension tube
- Estimated life is minimum 40000 cycles
- Q-version for noise sensitive applications (24 Vdc only)

General Specifications

Parameter	Electrak 050
Screw type	worm
Internally restrained	yes
Manual override	no
Dynamic braking	yes, at end of stroke
Holding brake	no, self-locking
End of stroke protection	internal limit switches
Mid stroke protection	overload clutch
Motor protection	auto reset thermal switch
Motor connection	flying leads and connector
Motor connector	Packard Electric Pack-Con male 8911773 with terminal 6294511 Mating connector: 8911772 with terminal 12040508
Certificates	CE optional* Non pot versions are RoHS compliant
Options	 potentiometer 10 kOhm** cross holes rotated 90° white housing


Performance Specifications

Parameter		Electrak 050
Maximum load, dynamic / static DE • • • 17W41 DE • • • 17W42 DE • • • 17W44	[lbf]	112 / 224 60 / 120 30 / 60
Speed, at no load / at maximum load DE •• - 17W41 DE •• - 17W42 DE •• - 17W44 DE24017W41 DE24017W42 DE24017W42 DE24017W44	[in/sec]	0.48 / 0.37 0.95 / 0.72 1.90 / 1.45 0.36 / 0.30 0.70 / 0.55 1.50 / 1.20
Available input voltages	[Vdc]	12, 24, 36
Standard stroke lengths	[in]	2, 4, 6, 8
Operating temperature limits	[°F]	-30-+180
Full load duty cycle @ 70 °F	[%]	25
End play, maximum	[in]	0.06
Restraining torque	[lbf-in]	0
Lead cross section	[AWG]	18
Lead length	[in]	6
Protection class standard version Q-version		IP66 IP51
Potentiometer resistance change DE ••• 17W41 DE ••• 17W42 DE ••• 17W44	[ohm/in]	560 556 540

* Contact customer support

** See performance specification table for resistance change per inch of travel.

12, 24 and 36 Vdc - load up to 112 lbf




Stroke (S)	[inch]	2	4	6	8
Retracted length (A)	[inch]	5.5	7.5	9.5	11.5
Retracted length, with potentiometer (A)	[inch]	6.75	8.75	10.75	-
Weight	[lb]	1.4	1.6	1.8	2.0
Weight with potentiometer	[lb]	1.6	1.8	2.0	-


Performance Diagrams

050, standard version

Speed and Current vs. Load



050, Q-version Speed and Current vs. Load




V: speed I: current F: load 1: speed 112 lbf 2: speed 60 lbf 3: speed 30 lbf 4: current 12 Vdc, 112 lbf * 5: current 24 Vdc, 112 lbf 6: current 12 Vdc, 60 lbf * 7: current 12 Vdc, 60 lbf 8: current 12 Vdc, 30 lbf 9: current 24 Vdc, 30 lbf * 12 Vdc not possible for Q-version.

12, 24 and 36 Vdc - load up to 112 lbf

Ordering Key

U	·				
1	2	3 4		5	6
DE24 -	17W44 -	06 FN		HH	N
1. Model and input volta DE12 - = Electrak 050, 12 DE24 - = Electrak 050, 24 DE36 - = Electrak 050, 36 DE24Q = Electrak 050, 24 2. Dynamic load capacit 17W41 - = 112 lbf 17W42 - = 60 lbf 17W44 - = 30 lbf	Vdc Vdc Vdc Vdc, Q-version	 3. Stroke 02 = 2 inch 04 = 4 inch 06 = 6 inch 08 = 8 inch 4. End of stroke limit switches and potentiometer FN = limit switches and no potentiometer 		5. Rear and front mounting HH = standard crosshole MH = crossholes rotated 6. Color N = black housing W = white housing 'Not possible in combination	e in both ends d 90°

Electrak 050



Connect the yellow lead to positive and red to negative to extend the actuator. Change polarity to retract the actuator. The potentiometer output has 0 ohm between white and red when the actuator is fully retracted.



Electrak 2 12 Vdc - load up to 250 lbf



Standard Features and Benefits

- Economical and robust actuator for medium loads
- Stainless steel extension tube
- Self-locking acme screw drive system
- Overload clutch for mid and end of stroke protection
- Motor with thermal switch
- Maintenance free

Performance Specifications

Parameter		Electrak 2
Maximum load, dynamic / static	[lbf]	250 / 1000
Speed, at no load / at maximum load D12-10A5 (high speed) D12-20A5 (standard speed)	[in/sec]	1.20 / 1.00 0.61 / 0.55
Available input voltages	[Vdc]	12
Standard stroke lengths	[in]	4, 8, 12, 18*, 24*
Operating temperature limits	[°F]	-15-+150
Full load duty cycle @ 77 °F	[%]	25
End play, maximum	[in]	0.08
Restraining torque	[lbf-in]	65
Lead cross section	[AWG]	14
Lead length	[in]	7.5
Protection class * Contact customer support		IP66

* Contact customer support


ParameterElectrak 2Screw typeacmeInternally restrainedno

General Specifications

Manual override	no, optional
Dynamic braking	no
Holding brake	no, self-locking
End of stroke protection	overload clutch
Mid stroke protection	overload clutch
Motor protection	auto reset thermal switch
Motor connection	flying leads and connector
Motor connector	Packard Electric 56 series 2984883 with terminal 2962987. Mating connector: 2973781 with terminal 2962573 (p/n 9100-448-001)
Certificates	CE optional*
Options	 potentiometer* manual override* limit switches*

* Contact customer support

12 Vdc - load up to 250 lbf




A2:	red	lead

Stroke (S)	[inch]	4	8	12
Retracted length (A)	[inch]	10.3	14.3	18.3
Weight	[lb]	10.0	10.7	11.4

Performance Diagrams

Life vs. Load




Ncycle: life in number of cycles (one cycle = extend and retract) F max: percent of maximum rated load

1: all models using the clutch at the end of stroke

- 2: standard speed model, 12 inch stroke
- 3: standard speed model, 8 inch stroke
- 4: high speed model, 12 inch stroke


5: high speed model, 8 inch stroke and

standard speed model, 4 inch stroke 6: high speed model, 4 inch stroke Duty Cycle vs. Load



ED: duty cycle in percent at 77° F F max: percent of maximum rated load 1: standard speed model 2: high speed model

Speed and Current vs. Load



V: speed I: current F: load

1: speed high speed model

2: speed standard speed model

3: current high speed model


4: current standard speed model

Electrak 2 12 Vdc - load up to 250 lbf

Ordering Key

or doring itoy			
1	2	3	4
D12 -	20A5 -	12	D
 Input voltage D12 - = 12 Vdc Dynamic load capacity and speed 10A5 - = 250 lbf, high speed 20A5 - = 250 lbf, standard speed 	3. Stroke ¹ 04 = 4 inch 08 = 8 inch 12 = 12 inch	lengths.	

Wiring Diagram



Connect the red lead to positive and yellow to negative to extend the actuator/rotate the output shaft in clockwise direction. Change polarity to retract the actuator/rotate the output shaft counterclockwise.



12, 24 and 36 Vdc - load up to 1500 lbf



Standard Features and Benefits

- Robust, strong and reliable
- Withstands very harsh environments
- Stainless steel extension tube
- Highly efficient ball screw drive system
- Overload clutch for mid and end of stroke protection
- Motor with thermal switch
- Maintenance free

General Specifications

Parameter	Electrak 10
Screw type	ball
Internally restrained	no
Manual override	no, optional
Dynamic braking	no
Holding brake	yes
End of stroke protection	overload clutch
Mid stroke protection	overload clutch
Motor protection	auto reset thermal switch
Motor connection	flying leads and connector
Motor connector	Packard Electric 56 series 2984883 with terminal 2962987. Mating connector: 2973781 with terminal 2962573 (p/n 9100-448-001)
Certificates	CE optional*
Options	 potentiometer* manual override* limit switches*


* Contact customer support

Performance Specifications

Parameter		Electrak 10
Maximum load, dynamic / static D •• -05B5 D •• -10(20)B5 Contact customer support	[lbf]	500 / 3000 1000 / 3000 1500 / 3000
Speed, at no load / at maximum load D •• -05B5 D •• -10B5 (high speed) D •• -20B5 (standard speed)	[in/sec]	2.40 / 1.40 1.30 / 0.80 0.60 / 0.45
Available input voltages	[Vdc]	12, 24, 36
Standard stroke lengths	[in]	4, 8, 12, 18*, 24*
Operating temperature limits	[°F]	-15-+150
Full load duty cycle @ 77 °F	[%]	25
End play, maximum	[in]	0.04
Restraining torque	[lbf-in]	100
Lead cross section	[AWG]	14
Lead length	[in]	7.5
Protection class		IP66

* Contact customer support


12, 24 and 36 Vdc - load up to 1500 lbf



Stroke (S)	[inch]	4	8	12
Retracted length (A)	[inch]	11.9	15.9	19.9
Weight	[lb]	11.3	12.0	12.7

Performance Diagrams

Life vs. Load



Ncycle: life in number of cycles

(one cycle = extend and retract)

2: 1000 lbf, 12 inch stroke

3: 1000 lbf, 8 inch stroke

4: 500 lbf, 12 inch stroke

5: 1000 lbf, 4 inch stroke


6: 500 lbf, 8 inch stroke

7: 500 lbf, 4 inch stroke

F max: percent of maximum rated load

1: all models using the clutch at the end of stroke

Duty Cycle vs. Load




ED: duty cycle in percent at 77° F F max: percent of maximum rated load

1: 1000 lbf, standard speed

2: 500 lbf





V: speed I: current F: load

1: speed 500 lbf

- 2: speed 1000 lbf, standard speed
- 3: speed 1000 lbf, high speed
- 4: current 500 lbf, 12 Vdc

5: current 500 lbf, 24 Vdc


- 6: current 1000 lbf, 12 Vdc, standard speed 7: current 1000 lbf, 24 Vdc, standard speed
- 8: current 1000 lbf, 12 Vdc, high speed
- 9: current 1000 lbf, 24 Vdc, high speed

12, 24 and 36 Vdc - load up to 1500 lbf

Ordering Key

5 7		
1	2	3
D12 -	20B5 -	04
1. Input voltage D12 - = 12 Vdc D24 - = 24 Vdc D36 - = 36 Vdc	05B5 - = 500 lbf	3. Stroke 04 = 4 inch 08 = 8 inch 12 = 12 inch

Wiring Diagram



Connect the red lead to positive and yellow to negative to extend the actuator/rotate the output shaft in clockwise direction. Change polarity to retract the actuator/rotate the output shaft counterclockwise.



115 and 230 Vac - load up to 1500 lbf



Standard Features and Benefits

- Strong and versatile heavy duty actuator
- High duty cycle
- Highly efficient ball screw drive system
- Overload clutch for mid and end of stroke protection
- Stroke lengths up to 36 inch
- Motor with thermal switch
- Maintenance free
- Large range of options

General Specifications

Parameter	Electrak PPA-AC
Screw type	ball
Internally restrained	no
Manual override	no, optional
Dynamic braking	no
Holding brake	yes
End of stroke protection	overload clutch
Mid stroke protection	overload clutch
Motor protection	auto reset thermal switch
Motor connection	flying leads
Motor connector	no
Certificates	RoHS compliant
Options	 end of stroke limit switches potentiometer encoder protective bellows anti-coast brake * electrical brake *** manual override****


* External capacitor, which is supplied with the actuator, is required to run

actuators with anti-coast brake option. See page 47 for capacitor dimensions. ** Only possible on 115 Vac models *** Contact customer support

Performance Specifications

Parameter		PPA-AC
Maximum load, dynamic / static PPA •• -18B65 PPA •• -58B65	[lbf]	500 / 3000 1500 / 3000
Speed, at no load / at maximum load PPA11-18B65 PPA22-18B65 PPA • • -58B65	[in/sec]	0.63 / 0.60 0.55 / 0.50 0.17 / 0.17
Available input voltages Single phase	[Vac]	115, 230
Input frequency 1 × 115 Vac model 1 × 230 Vac model	[Hz]	50/60 50/60
Standard stroke lengths	[in]	4, 8, 12, 18, 24, 36
Operating temperature limits	[°F]	-15-+150
Full load duty cycle @ 77 °F	[%]	30
End play, maximum	[in]	0.040
Restraining torque PPA •• -18B65 PPA •• -58B65	[lbf-in]	100 200
Lead cross section	[AWG]	18
Lead length	[in]	19.5
Protection class		IP22

115 and 230 Vac - load up to 1500 lbf



S: stroke

A: retracted length


B: retracted length to trunnions

C: motor length A1: housing dimensions for limit switch, encoder or potentiometer options

0. 1 (0)	F* 13		•	40	10		
Stroke (S)	[inch]	4	8	12	18	24	36
Retracted length (A) without options	[inch]	13.7	17.7	21.7	29.7	35.7	47.7
Retracted length (A) with limit switch, encoder or potentiometer	[inch]	15.7	19.7	23.7	31.7	37.7	49.7
Retracted length (B)	[inch]	8.8	12.8	16.8	24.8	30.8	42.8
Motor length (C) without brake	[inch]	9.5	9.5	9.5	9.5	9.5	9.5
Motor length (C) with anti-coast brake	[inch]	7.5	7.5	7.5	7.5	7.5	7.5
Motor length (C) with electrical brake	[inch]	11.0	11.0	11.0	11.0	11.0	11.0
Weight	[lb]	13.2	14.8	16.5	19.1	21.6	27.0
Weight with electrical brake	[lb]	14.6	16.2	17.9	20.5	23.0	28.4
Add on weight for limit switch, encoder or potentiometer	[lb]	1.7	1.7	1.7	1.7	1.7	1.7

Performance Diagrams

Speed and Current vs. Load



V: speed I: current F: load

1: speed 500 lbf, 115 Vac

- 2: speed 500 lbf, 230 Vac 3: speed 1500 lbf
- 4: current 500 lbf, 115 Vac
- 5: current 500 lbf, 230 Vac
- 6: current 1500 lbf, 115 Vac 7: current 1500 lbf, 230 Vac
- www.thomsonlinear.com

115 and 230 Vac - load up to 1500 lbf


Ordering Key

U	•				
1	2	3	4	5	6
PPA22 -	18B65 -	18	SB	ХХ	С
1. Model and input volta PPA11 - = Electrak PPA- PPA22 - = Electrak PPA- 2. Dynamic load capacit 18B65 - = 500 lbf 58B65 - = 1500 lbf	AC, 1 × 115 Vac AC, 1 × 230 Vac	3. Stroke 04 = 4 inch 08 = 8 inch 12 = 12 inch 18 = 18 inch 24 = 24 inch 36 = 36 inch 4. Brake option ¹ N - = no brake option SB = anti coast brake EB = electrical brake ²		 5. Feedback option XX = no feedback option LS = end of stroke limits PO = potentiometer³ HS = encoder HL = encoder + end of s 6. Bellows option X = no bellows C = bellows⁴ ¹See "Brake" in the Glos for more information. ²Only possible for 1 × 11 ³Not available with limit ⁴Only possible on 12 inc. 	switches troke limit switches ssary section on page 57 5 Vac models. switches.


115 and 230 Vac - load up to 1500 lbf

Wiring Diagram

Without brake or with electrical brake (dotted wiring)



With anti coast brake



* The actuator comes with prewired capacitor from factory.

** Electrical brake only possible on 115 Vac models.

**** The capacitor is supplied with the actuator but needs to be fitted by the customer externally. **** Supplied by customer.

For versions without brake or with electrical brake,

connect the red lead to L1 and yellow to L2 to extend the actuator. Change L1 from red to black lead to retract the actuator. If the actuator is equipped with an electrical brake the internal wiring automatically lifts the brake when the motor is energized. For versions with anti coast brake, connect the red lead to L1 and yellow to L2 to extend the actuator. Change L1 from red to blue lead to retract the actuator. Release the anti-coast brake by connecting black leads to L1 and L2.



115 and 230 Vac - load up to 1500 lbf



Standard Features and Benefits

- Robust, strong and reliable
- Stainless steel extension tube
- Highly efficient ball screw drive system
- Overload clutch for mid and end of stroke protection
- Heavy duty motor with thermal switch
- Anti-coast brake for repeatable positioning
- Maintenance free

General Specifications

Parameter	Electrak 5
Screw type	ball
Internally restrained	no
Manual override	no, optional
Dynamic braking	no
Holding brake	yes
End of stroke protection	overload clutch
Mid stroke protection	overload clutch
Motor protection	auto reset thermal switch
Motor connection	flying leads
Certificates	UL, CSA, CE optional*
Options	 potentiometer* manual override* limit switches*


* Contact customer support

Performance Specifications

Parameter		Electrak 5
Maximum load, dynamic / static A •• -05B5 A •• -10B5 Contact customer support	[lbf]	500 / 2500 1000 / 2500 1500 / 2500
Speed, at no load / at maximum load A •• -05B5 A •• -10B5	[in/sec]	2.10 / 1.70 1.10 / 1.00
Available input voltages** Single phase	[Vac]	115, 230
Input frequency 1 × 120 Vac model 1 × 230 Vac model	[Hz]	60 50/60
Standard stroke lengths	[in]	4, 8, 12, 18, 24
Operating temperature limits	[°F]	-15-+150
Full load duty cycle @ 77 °F	[%]	25
Maximum on time	[sec]	45
End play, maximum	[in]	0.04
Restraining torque	[lbf-in]	100
Lead cross section	[AWG]	18
Cable length	[in]	23
Protection class	25	IP55

** Capacitor required to run the actuator. 115 Vac = 35 μF , p/n 9200-448-002, 230 Vac = 10 μF , p/n 9200-448-003.

115 and 230 Vac - load up to 1500 lbf




A: retracted length

11:	cab	е		

Stroke (S)	[inch]	4	8	12	18	24
Retracted length (A)	[inch]	15.0	19.0	23.0	29.0	35.0
Weight	[lb]	14.4	15.2	16.1	17.3	18.6

Performance Diagrams

Life vs. Load




Ncycle: life in number of cycles (one cycle = extend and retract) F max: percent of maximum rated load

1: all models using the clutch at the end of stroke

2: all models using the anti-coast brake at the end of stroke only

Duty Cycle vs. Load




ED: duty cycle in percent at 77° F

1: 50 Hz input frequency

2: 60 Hz input frequency

F max: percent of maximum rated load

Speed and Current vs. Load



V: speed I: current F: load

- 2: speed 1000 lbf 3: current 500 lbf, 115 Vac
- 4: current 1000 lbf, 115 Vac
- 5: current 500 lbf, 230 Vac
- 6: current 1000 lbf, 230 Vac


^{1:} speed 500 lbf

115 and 230 Vac - load up to 1500 lbf

Ordering Key

5 /			
1	2	3	4
A12 -	05B5 -	04	D
1. Model and input voltage A12 - = Electrak 5, 1 × 115 Vac A22 - = Electrak 5, 1 × 230 Vac	2. Dynamic load capacity 05B5 - = 500 lbf 10B5 - = 1000 lbf	3. Stroke 04 = 4 inch 08 = 8 inch 12 = 12 inch 18 = 18 inch 24 = 24 inch	4. Shipment version ¹ D = distributor version ¹ Leave position blank for OEM version.

Electrak 5



Capacitor required to run the actuator. 115 Vac = 35 μF p/n 9200-448-002, 230 Vac = 10 μF p/n 9200-448-003. *

** Anti coast brake. *** Supplied by customer.

Connect the red lead to L1 and white to L2 to extend the actuator. Change L1 from red to black lead to retract the actuator. Release the anti coast brake by connecting orange lead to L1.



115 and 230 Vac - load up to 1500 lbf



Standard Features and Benefits

- Robust, strong and reliable
- Stainless steel extension tube
- Highly efficient ball screw drive system
- Electrical brake for accurate positioning
- Motor with thermal switch
- Adjustable end of stroke limit switches
- Potentiometer
- Universal mounting clamp for tube mounting available
- Maintenance free

General Specifications

Parameter	Electrak 205
Screw type	ball
Internally restrained	no
Manual override	no
Dynamic braking	no
Holding brake	yes
End of stroke protection	adjustable limit switches
Mid stroke protection	no
Motor protection	auto reset thermal switch
Motor connection	terminal strip in the housing
Cable entrance	1/2" NPT
Certificates	none
Options	none


Performance Specifications

Parameter		Electrak 205
Maximum load, dynamic ALP •• -05 ALP •• -10 Contact customer support	[lbf]	500 1000 1500
Maximum load, static tension ALP • • - • •	[lbf]	4000
Maximum load, static compression ALP •• - •• (stroke under 24 inch) ALP •• - •• (24 inch stroke)	[lbf]	4000 2500
Speed, at no load / at maximum load ALP •• -05 ALP •• -10	[in/sec]	2.05 / 1.75 1.10 / 0.90
Available input voltages* Single phase	[Vac]	115, 230
Input frequency 1 × 120 Vac model 1 × 230 Vac model	[Hz]	60 50/60
Standard stroke lengths	[in]	4, 8, 12, 18, 24
Operating temperature limits	[°F]	-15-+150
Full load duty cycle @ 77 °F	[%]	25
End play, maximum	[in]	0.035
Restraining torque	[lbf-in]	100
Max. terminal strip lead cross section	[AWG]	14
Protection class		IP55
Potentiometer	[k0hm]	10
Potentiometer resistance change	[ohm/in]	385

* Capacitor required to run the actuator. 115 Vac = 35 μF, p/n 9200-448-002, 230 Vac = 10 μF, p/n 9200-448-003.

Universal mounting kit. 9200-448-006

115 and 230 Vac - load up to 1500 lbf




Performance D	iagrams
---------------	---------

Life vs. Load

[lb]

25.5



Ncycle: life in number of cycles (one cycle = extend and retract) F max: percent of maximum rated load

- 1: 1000 lbf, 24 inch stroke
- 2: 1000 lbf, 18 inch stroke

Weight

3: 1000 lbf, 12 inch stroke


4: 1000 lbf, 8 inch stroke

5: 1000 lbf, 4 inch stroke

Duty Cycle vs. Load

27.5

29.5




ED: duty cycle in percent at 77° F F max: percent of maximum rated load 1: 50 Hz input frequency 2: 60 Hz input frequency

Speed and Current vs. Load

35.5

32.5



V: speed I: current F: load

- 1: speed 500 lbf
- 2: speed 1000 lbf
- 3: current 500 lbf, 115 Vac
- 4: current for 1000 lbf, 115 Vac 5: current 500 lbf, 230 Vac


5: current 500 lbf, 230 Vac 6: current 1000 lbf, 230 Vac

115 and 230 Vac - load up to 1500 lbf

Ordering Kev

5			
1	2	3	4
ALP22 -	10B5 -	04	
1. Model and input voltage ALP12 - = Electrak 205, 1 × 115 Vac ALP22 - = Electrak 205, 1 × 230 Vac	2. Dynamic load capacity 05B5 - = 500 lbf 10B5 - = 1000 lbf	3. Stroke 04 = 4 inch 08 = 8 inch 12 = 12 inch 18 = 18 inch 24 = 24 inch	4. Shipment version ¹ D = distributor version ¹ Leave position blank for OEM version.

Electrak 205



* Capacitor required to run the actuator. 115 Vac = 35 $\mu F, \, p/n$ 9200-448-002, 230 Vac = 10 $\mu F, \, p/n$ 9200-448-003.

** LSR = end of stroke limit switch in retracted position, LSE = end of stroke limit switch in extended position.

*** Electrical brake.

The terminal strip is accessed by opening the rear cover of the actuator housing. Connect terminal 8 to L1 and terminal 2 to L2 to extend the actuator. Change L1 from terminal 8 to 13 to retract the actuator. Release the anti coast brake by connecting terminal 1 to L1. The potentiometer output is connected to terminals 14, 15 and 16.

Electrak Non-driven Actuator PPA-M

Load up to 1500 lbf



Standard Features and Benefits

- Actuator with double input shafts to which a customer supplied motor or/and an intermediate shaft can be mounted
- Can be operated manually
- Robust and versatile
- Withstands very harsh environments
- Highly efficient ball screw drive system
- Holding brake prevents back driving
- Trunnion to clevis mounting
- Maintenance free

General Specifications

Parameter	Electrak PPA-M
Screw type	ball
Internally restrained	no
Manual override	no*
Holding brake	yes
End of stroke protection	no
Mid stroke protection	no
Certificates	-
Options	protective bellows


* Either of the two input shafts can be used for manual operation if both shafts are not connected to a motor or an intermediate shaft.

Performance Specifications

Parameter		PPA-M
Maximum load, dynamic / static	[lbf]	1500 / 3000
Maximum speed at max. load	[in/sec]	0.33
Maximum input torque	[lbf-in]	80
Maximum input speed	[rpm]	100
Standard stroke lengths	[in]	4, 8, 12, 18, 24, 36
Operating temperature limits	[°F]	-15-+150
End play, maximum	[in]	0.04
Restraining torque	[lbf-in]	200

Electrak Non-driven Actuator PPA-M

Load up to 1500 lbf




Stroke (S)	[inch]	4	8	12	18	24	36
Retracted length (A)	[inch]	14.8	18.8	22.8	30.8	36.8	48.8
Retracted length to trunnions (B)	[inch]	8.8	12.8	16.8	24.8	30.8	42.8
Weight	[lb]	7.6	9.2	10.6	13.5	16.0	21.4

Synchronous Operation

Two or more PPA-M actuators can easily be mechanically linked for synchronous operation. They can either be driven directly by motor (1) or by the PPA synchronous operation kit (2). Intermediate shafts, couplings and motors (white details) are supplied by the customer. For more information about the PPA synchronous operation kit, see Accessories and Spare Parts on page 46.

2. With PPA synchronous operation kit

1. With motor



Electrak Non-driven Actuator PPA-M

Load up to 1500 lbf

Ordering Key

or doring itoy			
1	2	3	4
PPA00 -	01B65 -	24	N-XXX
1. Model PPA00 - = Electrak PPA-M	2. Dynamic load capacity 01B65 - = 1500 lbf	3. Stroke 04 = 4 inch 06 = 6 inch 08 = 8 inch 12 = 12 inch 18 = 18 inch 24 = 24 inch 36 = 36 inch	4. Bellows option N-XXX = no bellows N-XXC = bellows

Rotary Actuator DGB

12, 24 and 36 Vdc - load torque up to 100 lbf-in



Standard Features and Benefits

- Rotary actuators for industrial and outdoor use
- Easy and fast clevis mounting
- Overload clutch
- Thermal protected motor
- Manual override or dual output shafts as option

Performance Specifications

Parameter		DGB
Maximum load torque	[lbf-in]	100
Speed, at no load / at maximum load D •• -21GB D •• -30GB ¹	[rpm]	200 / 80 140 / 75
Available input voltages	[Vdc]	12, 24, 36
Weight D •• - ••• - XXCL D •• - ••• - XXMO D •• - ••• - XXDS	[lb]	7.7 7.7 7.7
Operating temperature limits	[°F]	-15-+150
Full load duty cycle @ 77 °F	[%]	25
Lead cross section	[AWG]	14
Lead length	[in]	7.0
Protection class		IP56

General Specifications


Parameter	DGB
Manual override	no
Dynamic braking	no
Holding brake	yes
Overload protection	overload clutch
Motor protection	auto reset thermal switch
Motor connection	flying leads and connector
Motor connector	Packard Electric 56 series 2984883 with terminal 2962987. Mating connector: 2973781 with terminal 2962573 (p/n 9100-448-001)
Certificates	CE optional*
Options	 manual override dual output shafts other speeds*

* Contact customer support


Rotary Actuator DGB

12, 24 and 36 Vdc - load torque up to 100 lbf-in

D • • - 21GB-XXCL, D • • - 30GBXXCL (clevis mount)




D • • - 21GB-XXDS (dual output shafts)



Performance Diagrams


Speed and Current vs. Load



V: speed l: current F: load 1: speed D12-21GB 2: speed D12-30GB 3: current D12-21GB 4: current D12-30GB

Contact customer support for data on 24 and 36 Vdc models (D •• -30GB is not available for 36 Vdc). www.thomsonlinear.com

D • • - 21GBXXMO (manual override)




Rotary Actuator DGB

12, 24 and 36 Vdc - load torque up to 100 lbf-in

Ordering Key		
1	2	3
D36 -	21GB -	XXCL
1. Input voltage D12 - = 12 Vdc D24 - = 24 Vdc D36 - = 36 Vdc	2. Load torque capacity and no load speed 21GB - = 100 lbf-in, 200 rpm 30GB - = 100 lbf-in, 140 rpm ¹	3. Version XXCL = one output shaft + clevis mount XXMO = one output shaft + manual override XXDS = dual output shafts 'Not possible with 36 Vdc input voltage.





Connect the red lead to positive and yellow to negative to extend the actuator/rotate the output shaft in clockwise direction. Change polarity to retract the actuator/rotate the output shaft counterclockwise.



Switches

DPDT Switch



- Robust switch
- Double pole, double throw (DPDT)
- 15 A rating at 270 Vac
- Center "off"
- Two momentary contacts
- Wiring diagram on label

Specifications


Parameter		DPDT Switch
Maximum voltage	[Vac]	270
Maximum current	[A]	15
Part number		830-8004-016


Actuator Compatibility


Electrak 1, Electrak 1SP, Electrak 050, Electrak 2, Electrak PPA-DC, Electrak 10, Electrak Pro, Electrak PPA-AC, Electrak 5, Electrak 205, DGB

Wiring Diagram

Dimensions







Switches

DPDT Switch Box



- Robust rocker switch mounted in an enclosure
- Double pole, double throw (DPDT)
- 15 A rating at 270 Vac
- Center "off"
- Two momentary contacts
- Mounting bracket included
- Wiring diagram on label

www.thomsonlinear.com


Specifications

Parameter		DPDT Box
Maximum voltage	[Vac]	270
Maximum current	[A]	15
Protection class		NEMA 1
Part number		6932-101-054


Actuator Compatibility

Electrak 1, Electrak 1SP, Electrak 050, Electrak 2, Electrak PPA-DC, Electrak 10, Electrak Pro, Electrak PPA-AC, Electrak 5, Electrak 205, TC16, DMD, DMA, LM80-H, LM80-V, DGB

Wiring Diagram



Note: some AC actuators require a capacitor in the wiring to run. This capacitor will not fit in this box due to space limitations.






Electronic Controls

Control MCS-2041



- Robust and compact metal enclosure with a front panel extend and retract rocker switch
- Prewired internal capacitor
- Fuse protects actuator in case of stalling caused by overload
- "Power On" light illuminates whenever power applied to the control
- Terminal strip for easy electrical connection
- The switch controls both the actuator motor and its anti coast brake to provide optimum performance

Dimensions




Specifications

Parameter		MCS-2041
Input voltage	[Vac]	1 × 115
Input frequency	[Hz]	50/60
Output voltage	[Vac]	1 × 115
Maximum output current	[A]	15
Protection class		NEMA 1
Part number		6932-448-010

Actuator Compatibility

Electrak 5

Wiring Diagram




Electronic Controls

Control MCS-2051



- Control designed to operate an Electrak 205 actuator
- Robust metal enclosure with front cover mounted membrane switches and LED indicator lights for extend, retract, jog, run and remote control
- Emergency stop/off pushbutton remains in position when activated
- LCD display shows the extension tube position
- Internal "Run" mode jumper which causes the actuator to reverse automatically upon reaching the extend end of stroke limit switch. Reverse motion continues until reaching the retract end of stroke limit switch
- The control provides an analog output signal for an external customer provided control/meter
- Inputs for external extend and retract switches
- Inputs for two external end of stroke limit switches
- Dynamic braking
- Terminal strip for easy electrical connection

Dimensions



A1: Cable entrance, 1/2 inch standard conduit (2 ×)


Specifications

Parameter		MCS-2051
Input voltage	[Vac]	1 × 115
Input frequency	[Hz]	50/60
Output voltage	[Vac]	1 × 115
Maximum actuator output current	[A]	8
Analog output signal	[mA]	4 - 20
Protection class		NEMA1
Part number		6932-448-015

Actuator Compatibility

Electrak 205

Wiring Diagram



^{*} Inserting jumper J4 causes the actuator to reverse automatically upon reaching the extend end of stroke limit switch. Reverse motion continues until reaching the retract end of stroke limit switch.

USA, CANADA and MEXICO

Thomson 203A West Rock Road Radford, VA 24141, USA Phone: +1 540 633 3549 Fax: 1 540 633 0294 E-mail: thomson@thomsonlinear.com Literature: literature.thomsonlinear.com

EUROPE

United Kingdom Thomson

Office 9, The Barns Caddsdown Business Park Bideford, Devon, EX39 3BT Phone: +44 1271 334 500 E-mail: sales.uk@thomsonlinear.com

Germany

Thomson Nürtinger Straße 70 72649 Wolfschlugen Phone: +49 7022 504 403 Fax: +49 7022 504 405 E-mail: sales.germany@thomsonlinear.com

France

Thomson Phone: +33 243 50 03 30 Fax: +33 243 50 03 39 E-mail: sales.france@thomsonlinear.com

Italy

Thomson Via per Cinisello 95/97 20834 Nova Milanese (MB) Phone: +39 0362 366406 Fax: +39 0362 276790 E-mail: sales.italy@thomsonlinear.com

Spain

Thomson E-mail: sales.esm@thomsonlinear.com

Sweden

Thomson Estridsväg 10 29109 Kristianstad Phone: +46 44 24 67 00 Fax: +46 44 24 40 85 E-mail: sales.scandinavia@thomsonlinear.com

ASIA

Asia Pacific Thomson E-mail: sales.apac@thomsonlinear.com

China

Thomson Rm 805, Scitech Tower 22 Jianguomen Wai Street Beijing 100004 Phone: +86 400 606 1805 Fax: +86 10 6515 0263 E-mail: sales.china@thomsonlinear.com

India

Thomson c/o Portescap India Pvt Ltd 1 E, first floor, Arena House Road no 12, Marol Industrial Area, Andheri (E), Mumbai 400093 India E-mail: sales.india@thomsonlinear.com

Japan

Thomson Minami-Kaneden 2-12-23, Suita Osaka 564-0044 Japan Phone: +81 6 6386 8001 Fax: +81 6 6386 5022 E-mail: csjapan@scgap.com

South Korea

Thomson 3033 ASEM Tower (Samsung-dong) 517 Yeongdong-daero Gangnam-gu, Seoul, South Korea (06164) Phone: + 82 2 6001 3223 & 3244 E-mail: sales.korea@thomsonlinear.com

SOUTH AMERICA

Brasil Thomson Av. João Paulo Ablas, 2970 Jardim da Glória - Cotia SP - CEP: 06711-250 Phone: +55 11 4615 6300 E-mail: sales.brasil@thomsonlinear.com

www.thomsonlinear.com

Linear_Actuators_CTEN-0005-07 | 20190508TJ Specifications are subject to change without notice. It is the responsibility of the product user to determine the suitability of this product for a specific application. All trademarks property of their respective owners. ©2019 Thomson Industries, Inc.



Linear Motion. Optimized."